

## AXIS P1435-E Network Camera

Compact, cost-effective and flexible HDTV surveillance with WDR

With features such as Lightfinder and WDR – Forensic Capture, the AXIS P1435-E bullet camera provides excellent image quality in HDTV 1080p resolution, even in complex light conditions. The camera features corridor format, pixel counter, remote zoom and focus, as well as P-Iris control – ensuring optimal depth of field, resolution, image contrast and clarity. The I/O port can be used for notification to an alarm panel or control of a relay. Axis' Zipstream technology reduces bandwidth and storage requirements. The outdoor-ready camera comes with an adjustable weather shield.

- > [Lightfinder and WDR – Forensic Capture](#)
- > [Axis' Zipstream technology](#)
- > [HDTV 1080p at up to 60 fps](#)
- > [I/O support](#)
- > [Edge storage](#)



# AXIS P1435-E Network Camera

Camera		Notification: email, HTTP, HTTPS and TCP and SNMP trap External output activation Video recording to edge storage Pre- and post-alarm video buffering WDR mode PTZ control, Overlay text
Image sensor	Progressive scan CMOS 1/2.8"	
Lens	3–10.5 mm, F1.4: Horizontal field of view 95° – 35° Vertical field of view 51° – 20° Varifocal, Autofocus, Remote focus and zoom, P-Iris control, IR corrected	
Day and night	Automatically removable infrared-cut filter	
Minimum illumination	3–10.5 mm, F1.4: Color: 0.12 lux at 30 fps Color: 0.24 lux at 60 fps B/W: 0.01 lux at 30 fps B/W: 0.02 lux at 60 fps WDR off: 0.07 lux WDR on: 0.08 lux	
Shutter time	1/66500 s to 2 s	
Video		
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline, Main and High Profiles Motion JPEG	
Resolutions	HDTV 1080p 25/30 fps (WDR): 1920x1080 to 160x90 HDTV 1080p 50/60 fps (no WDR): 1920x1080 to 160x90 Meets relevant parts of SMPTE 274M (HDTV 1080p)	
Frame rate	Up to 50/60 fps (50/60 Hz, no WDR) in all resolutions	
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Axis' Zipstream technology in H.264 Controllable frame rate and bandwidth VBR/MBR H.264	
Image settings	Manual shutter time, Compression, Color, Brightness, Sharpness, White balance, Exposure control, Exposure zones, Fine tuning of behavior at low light, Text and image overlay, Privacy masks Wide Dynamic Range – Forensic Capture: Up to 120 dB depending on scene, Mirroring of images Rotation: 0°, 90°, 180°, 270°, including Corridor Format	
Pan/Tilt/Zoom	Digital PTZ	
Network		
Security	Password protection, IP address filtering, HTTPS <sup>a</sup> encryption, IEEE 802.1X <sup>a</sup> network access control, Digest authentication, User access log	
Supported protocols	IPv4/v6, HTTP, HTTPS <sup>a</sup> , SSL/TLS <sup>a</sup> , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP™, SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH	
System integration		
Application Programming Interface	Open API for software integration, including VAPIX® and AXIS Camera Application Platform; specifications at <a href="http://www.axis.com">www.axis.com</a> AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF® Profiles S and G, specifications at <a href="http://www.onvif.org">www.onvif.org</a>	
Analytics	AXIS Video Motion Detection 3 Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see <a href="http://www.axis.com/acap">www.axis.com/acap</a>	
Event triggers	Analytics Detectors: Day/Night Mode, Live Stream Accessed, Tampering Hardware: Network, Temperature Input Signal: Manual Trigger, Virtual Inputs Storage: Disruption, Recording System: System Ready Time: Use Schedule, Recurrences	
Event actions	File upload: FTP, SFTP, HTTP, HTTPS network share and email	
Built-in installation aids	Pixel counter, Remote zoom (3–10.5 mm 3.5x optical), Remote focus	
Data streaming	Event data	
General		
Casing	IP66-, IP67-, NEMA 4X-rated casing (polyester polycarbonate blend)	
Sustainability	PVC free	
Memory	512 MB RAM, 256 MB Flash	
Power	Power over Ethernet IEEE 802.3af/802.3at Type 1 Class 3 Typical 2.3 W, max 11 W	
Connectors	RJ45 10BASE-T/100BASE-TX PoE I/O: 4-pin terminal block for 1 alarm input and 1 output	
Storage	Support for microSD/microSDHC/microSDXC card Support for recording to dedicated network-attached storage (NAS) For SD card and NAS recommendations see <a href="http://www.axis.com">www.axis.com</a>	
Operating conditions	-30 °C to 60 °C (-22 °F to 140 °F) Humidity 10–100% RH (condensing)	
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)	
Approvals	EN 61000-6-1, EN 61000-6-2, EN 50121-4, IEC 62236-4, EN 55024, FCC Part 15 Subpart B Class B, ICES-003 Class B, VCCI Class B, RCM AS/NZS CISPR 22 Class B, KCC KN22 Class B, KN24, IEC/EN/UL 60950-1, IEC/EN/UL 60950-22, IEC/EN 60529 IP66/IP67, NEMA 250 type 4X, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-27 EN 55022 Class B	
Weight	With weather shield: 800 g (1.75 lb)	
Dimensions	Ø132 x 260 mm (Ø5 3/16 x 10 1/4 in)	
Included accessories	Mounting bracket, Drill template, Installation Guide, Windows decoder 1-user license AXIS Weather Shield L	
Optional accessories	AXIS T94F01M J-Box/Gang Box Plate AXIS T91A47 Pole Mount AXIS T94P01B Corner Bracket AXIS T94F01P Conduit Back Box AXIS Weather Shield K Axis PoE Midspans For more accessories, see <a href="http://www.axis.com">www.axis.com</a>	
Video management software	AXIS Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on <a href="http://www.axis.com/techsup/software">www.axis.com/techsup/software</a>	
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese	
Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see <a href="http://www.axis.com/warranty">www.axis.com/warranty</a>	

a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (<http://www.openssl.org/>), and cryptographic software written by Eric Young ([ey@cryptsoft.com](mailto:ey@cryptsoft.com)).

## Environmental responsibility:

[www.axis.com/environmental-responsibility](http://www.axis.com/environmental-responsibility)