

Environment Monitoring System with 1-Wire Sensor Interface

ENVIROMUX®

**Monitor and manage environmental and security conditions over IP.
Provides early warnings before critical events turn into disaster.**

Environment Monitoring

- Temperature
- Humidity
- Water Leaks
- Air Flow
- Power
- Motion / Intrusion
- Vibration
- Smoke / Carbon Monoxide

Alert Notifications

- Email
- SNMP
- Web Page
- SMS

Key Features

- Monitor and manage environmental and security conditions over IP.
- Sensors supported:
 - 2 digital inputs sensitive to contact closure.
 - 2 RJ11 6P4C connectors for daisy-chaining 1-wire temperature/humidity/dew point, thermocouple, or digital input expanders in any combination.
 - ♦ Up to 24 temperature, thermocouple, or any single reading 1-wire sensor can be connected between both RJ11 connectors.
 - ♦ Up to 8 temperature/humidity/dew point combination 1-wire sensors can be connected between both RJ11 connectors. Each temperature/humidity/dew point sensor is equivalent to 3 single reading sensors.
 - ♦ Up to 12 ENVIROMUX-DI2-1W digital input expanders can be connected between both RJ11 connectors to allow a maximum of 24 additional digital inputs. Each ENVIROMUX-DI2-1W is equivalent to 2 single reading sensors.
 - ♦ Maximum cable length supported on each connector is up to 600ft (183 m) depending on the configuration and number of connected sensors.
 - ♦ Use RJ11 splitters (RJ11-3JCK) to daisy-chain 1-wire sensors (sold separately).
- Sensors are hot pluggable.
 - The sensors will automatically be detected on power up or a Detect Devices button on the summary page can be selected when logged into the unit.
- Monitors (ping) up to 4 IP network devices – alerts are sent if devices are not responding.
- Sensor conditions can be configured to trigger alerts by themselves, and/or be used in combination with other alerts to trigger one Smart Alert.
- Supports 4 IP network video cameras for live view of any facility.
- USB port for connecting USB modem.
- Dual redundant power supplies for connection to two separate power sources.
 - The second power supply is sold separately.
- Optional Power over Ethernet (POE).
- Integrates with various Open Source SNMP monitoring packages – Nagios and MRTG
- (Coming Soon) Optional intuitive graphical management software provides an easy-to-use, unified interface for both monitoring and configuring up to 3,000 ENVIROMUX units and all connected sensors.
- Security: HTTPS, SSLv3, AES 256-bit encryption, 16-character username/password authentication, user account restricted access rights.
- Ideal for a wide range of applications including IT infrastructure monitoring, cold storage/freezer monitoring, or any unmanned area that needs to be monitored.




ENVIROMUX-1W



The ENVIROMUX® Environment Monitoring System with 1-Wire Sensor Interface monitors critical environmental conditions, such as temperature, humidity, liquid water presence, power, intrusion, and smoke. When a sensor goes out of range of a configurable threshold, the system will notify you via email, web page, network management (SNMP), and/or SMS messages (via external USB 3G modem).

The system supports 24 single reading 1-wire sensors in any combination – temperature, humidity, dew point, thermocouple or digital inputs-and 2 separate digital inputs.



Environment Monitoring System with 1-Wire Sensor Interface

ENVIROMUX®

**Monitor and manage environmental and security conditions over IP.
Provides early warnings before critical events turn into disaster.**

	ENVIROMUX-1W
RJ11 Sensor Ports	2 RJ11 6P4C one-wire connectors <ul style="list-style-type: none"> Daisy-chain up to 24 single reading sensors total. Maximum cable length supported on each connector is up to 600ft depending on the configuration and number of connected sensors. Up to 24 temperature, thermocouple, or any single reading 1-wire sensor can be connected between both RJ11 connectors. Up to 8 temperature/humidity/dew point combination 1-wire sensors can be connected between both RJ11 connectors. Each temperature/ humidity/ dew point sensor is equivalent to 3 single reading sensors. Up to 12 ENVIROMUX-DI2-1W digital input expanders can be connected between both RJ11 connectors to allow a maximum of 24 additional digital inputs. Each ENVIROMUX-DI2-1W is equivalent to 2 single reading sensors.
Digital Inputs – Screw Terminal Pair	2
Alerts	4 Methods
Email	✓
Web Page	✓
SNMP traps (v1, v2c)	✓
SMS Messages	✓ – via external USB 3G modem (not included)
Smart Alerts	1
IP Cameras	✓ – up to 4 cameras
Control Methods	3 Methods
Web Interface	✓
Telnet	✓
SNMP Monitoring (v1, v2c)	✓
USB Ports for Modem	1
Expandable (Coming Soon)	Up to 3,000 units via optional management software
Flash Upgradable	✓
Protocols Supported	HTTP/HTTPS, SNMP V1/V2c, SMTP, TCP/IP, Syslog, SNTP, DHCP, SSLv3, AES 256-bit, 3DES, Blowfish, RSA, EDH-RSA, Arcfour
Restore Defaults Button	✓
Operating & Storage Temperature	-40 to 167°F (-40 to 75°C)
Operating & Storage Relative Humidity	0 to 90% non-condensing RH
Monitor (Ping) IP Devices	✓ – up to 4 network devices
Power	Optional Power-over-Ethernet (POE)
	Dual DC power
	<ul style="list-style-type: none"> 120 to 240 VAC at 50 or 60 Hz via AC adapter. <ul style="list-style-type: none"> ENVIROMUX-1W: Includes one country-specific AC adapter. The second AC adapter is sold separately. ENVIROMUX-1WP: Country-specific AC adapters are sold separately
	5.5VDC input voltage
MTBF	ENVIROMUX-1W: 703,871 hours
Dimensions WxDxH (in)	4x3.65x1.37
Mounting	Mounting holes to match rack hole spacing
Regulatory Approvals	CE, RoHS
Warranty	2 years