

μATS - HV-Y



The **Zonit Micro Automatic Transfer Switch (μATS™)** is the world's smallest ATS and solves the problem of supplying A+B redundant power to single power supply devices. The μATS™ monitors the quality of the power on the A side and will transfer to the B side if the quality is not within acceptable limits. The μATS™ will switch back to A when it returns and is of good quality. The μATS™ will transfer regardless of phase angle between A and B.




The μATS™ L-Y versions allow a single μATS™ unit to protect 2 or 3 devices from a power failure simultaneously. Please note that the total load of all served devices cannot exceed the rated load of the μATS™.

- **Warranty:** 3 years
- **Made in USA**

Available Connectors and Corded Outputs

Input

Output



SPECIFICATIONS

ELECTRICAL

Input Voltage	208 to 240
Max Operating Amperage	8 Amps
Input Frequency	60 Hz
Input Cords	2', 4' or 6' 18 AWG/3 SJTW 105°C
Input Connectors	IEC C-14, C16, zLock, NEMA 6-15P and L6-15P
Output Cord	~10" or 6' 18 AWG/3SJTW 105°C
Output Connectors	IEC C-13, C15, zLock, NEMA 6-15P and L6-15P
Internal Overload Protection	Internal Virtual Circuit Breaker with Reset Button
Transfer Time	9 to 11 ms
Quiescent Power Consumption	5 ma on A side 13 ma on B side

PHYSICAL

Dimensions (L x W x D)		.75" x 1.6" x 4.25" (19 x 40 x 108 mm)		
	IN/ OUT	2'	4'	6'
Unit Weight (C14 in, C13 out)	10"	.75lb (.34 kg)	1 lb (.45 kg)	1.2 lb (.54 kg)
	6"	1 lb (.45 kg)	1.3 lb (.59 kg)	1.6 lb (.73 kg)
Shipping Weight (C14 in, C13 out)	10"	1 lb (.45 kg)	1.2 lb (.54 kg)	1.5 lb (.68 kg)
	6"	1.2 lb (.54 kg)	1.5 lb (.68 kg)	1.8 lb (.82 kg)

ENVIRONMENTAL

Elevation – Operating	10,000 ft. (3 Km), max
Elevation – Storage	50,000 ft. (315 Km), max
Temperature – Operating	32 to 110°F (0 to 43°C)
Temperature – Storage	0 to 110°F (-18 to 43°C)
Operating Humidity	0 to 95% Non-condensing

APPROVALS

Safety Verification	cULus CE File E340237
WEEE	