

AXIS V5915 PTZ Network Camera

Live streaming with high-quality audio and HDTV 1080p

AXIS V5915 offers HDTV 1080p resolution with smooth pan/tilt/zoom, high quality audio streaming in stereo, and powerful 30x zoom. It can stream and webcast audio and video in a variety of applications, such as Microsoft Lync and Skype. The open interface makes it easy to integrate with other systems. AXIS Streaming Assistant enables easy setup of peer-to-peer video conference systems and live production to a larger audience. Audio connectors meet most requirements for professional audio processing, enabling connection of high-quality microphones and speakers, and SDI connectors allow integration into other live production systems. AXIS V5915 can also be connected to a monitor through HDMI.

- > **HDTV video streaming**
- > **30x optical zoom with autofocus**
- > **Smooth pan tilt and zoom**
- > **CD-quality stereo audio**
- > **Support for SDI and HDMI**



AXIS V5915 PTZ Network Camera

Models	AXIS V5915 50 Hz AXIS V5915 60 Hz	Audio output	3.5 mm unbalanced stereo output Output impedance: < 100 Ohm, short circuit proof Signal-to-Noise ratio: > 87 dB Bandwidth: 20 Hz – 20 kHz, may be limited by sample rate THD+N: < 0.03% @ 10 kOhm load Maximum input level: > 0.707 Vrms SDI THD+N: < 0.03% Bandwidth: 20 Hz – 20 kHz Signal-to-Noise ratio: > 87 dB @ 0 dB gain, > 83 dB @ 30 dB gain HDMI THD+N: < 0.03% Bandwidth: 20 Hz – 20 kHz Signal-to-Noise ratio: > 87 dB @ 0 dB gain, > 83 dB @ 30 dB gain
Camera		Audio input/output	External stereo microphone input or line input, line output
Image sensor	Progressive scan RGB CMOS 1/2.8"	Network	
Lens	4.3–129 mm, F1.6–4.7 Horizontal angle of view: 63.7°–2.3° Vertical angle of view: 34.5°–1.2° Autofocus, P-iris control	Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X ^a network access control, Digest authentication, User access log, Centralized certificate management
Day and night	Automatically removable infrared-cut filter	Supported protocols	IPv4/v6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH, HDMI 1.4 3G-SDI
Minimum illumination	Color: 1.0 lux at 30 IRE F1.6 B/W: 0.03 lux at 30 IRE F1.6	System integration	
Shutter time	1/10000 s to 1 s	Application Programming Interface	Open API for software integration, including VAPIX [®] and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection. ONVIF Profile S, specification at www.onvif.org
Pan/Tilt/Zoom	Pan: ±170°, 0.2–100°/s Tilt: –20° – 90°, 0.2–90°/s Zoom: 30x Optical, 12x Digital, Total 360x 256 presets positions, Control queue, On-screen directional indicator, Adjustable zoom speed	Analytics	Support for AXIS Camera Application Platform enabling installation of third-party applications, see www.axis.com/acap
Video		Event triggers	Detectors: Live Stream Accessed, Motion Detection, Audio Detection Hardware: Network Input Signal: Manual Trigger, Virtual Inputs, Digital Inputs PTZ: Error, Moving, Preset Reached, Ready Storage: Disruption, Recording System: System Ready Time: Recurrence, Use Schedule
Video compression	H.264 High, Baseline and Main profile (MPEG-4 Part 10/AVC), Motion JPEG	Event actions	Day/night mode, overlay text, video and audio recording to edge storage, pre- and post-alarm video buffering, PTZ preset, external output activation, play audio clip, send SNMP trap File upload via FTP, SFTP, HTTP, HTTPS, network share and email, Send video clip Notification via email, HTTP, HTTPS and TCP
Resolutions	1920x1080 HDTV 1080p to 160x90 HDMI/SDI Output: 1080p@50/60 fps (50/60 Hz) 1080i@50/60 fps (50/60 Hz) 720p@50/60 fps (50/60 Hz)	Data streaming	Event data
Frame rate	Up to 50/60 fps	Built-in installation aids	Pixel counter
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG, Controllable frame rate and bandwidth, VBR/MBR H.264, HDMI 3G-SDI, SMPTE 292-1, SMPTE 424 Level A	General	
Image settings	Compression, Color, Brightness, Sharpness, White balance, Exposure control, Exposure zones, Backlight compensation, Defogging, Noise reduction, Electronic image stabilization, Text and image overlay (over Ethernet) Rotation: 0°, 180° WDR-Dynamic Capture: 120dB	Casing	ASA plastic cover black and white Color: White NCS S 1002-B
Audio		Sustainability	PVC free
Audio streaming	Two-way, Stereo	Memory	1 GB RAM, 512 MB Flash
Audio compression	SDI: AES3 24 bit, 48 kHz HDMI: LPCM Network: AAC LC 8/16/32/48 kHz, G.711 PCM 8 kHz, G.726 ADPCM 8 kHz, Opus 8/16/48 kHz, Configurable bit rate	Power	8–28 V DC (12 V power supply included) typical 12 W, max 21 W
Audio input	XLR balanced mono input (left/right) Microphone phantom power 48 V Balanced external microphone (mono) Balanced line level (mono) Maximum input level: 4.4 Vrms Bandwidth: 20 Hz – 20 kHz, may be limited by sample rate THD+N: < 0.03% Signal-to-Noise ratio: > 85 dB @ 0 dB gain, > 78 dB @ 30 dB gain 3.5 mm unbalanced stereo input Microphone Power 5 V via 2.2 kOhm Unbalanced external microphone (stereo) Unbalanced line (stereo) Line input impedance: < 1.7 kOhm Maximum input level: 2.2 Vrms THD+N: < 0.03% Signal-to-Noise ratio: > 87 dB @ 0 dB gain, > 83 dB @ 30 dB gain Bandwidth: 20 Hz – 20 kHz, may be limited by sample rate	Connectors	RJ45 10BASE-T/100BASE-TX Terminal block for 2 configurable alarm input/output 3.5 mm stereo mic/line in, 3.5 mm stereo line out XLR-3 (left + right) mic/line in (with 48 V phantom power) HDMI Type A, BNC for SDI, Terminal block for DC power
		Storage	Support for microSD/microSDHC/microSDXC card Support for recording to dedicated network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com
		Operating conditions	0 °C to 40 °C (32 °F to 104 °F) Humidity 10–85% RH (non-condensing)
		Storage conditions	–20 °C to 60 °C (–4 °F to 140 °F) Humidity 10 – 85% RH (non-condensing)

Approvals	EN 55022 Class A, EN 55024, EN 61000-6-1, EN 61000-6-2, EN 61000-3-2, EN 61000-3-3, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, KCC KN 22 Class A, KN 24, C-tick AS/NZS CISPR 22 Class A, IEC/EN/UL 60950-1, EN 50581
Dimensions	180 x 136 x 136 mm (7.1 x 5.4 x 5.4 in)
Weight	1.49 kg (3.3 lb)
Included accessories	Power supply, Wall/Ceiling mount, Terminal connector for I/O, Installation Guide, Windows decoder 1-user license
Optional accessories	AXIS T8353B Microphone Phantom Power AXIS T8310 Video Surveillance Control Board

Languages English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese

Warranty Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty

- a. *This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (www.openssl.org), and cryptographic software written by Eric Young (eay@cryptsoft.com).*

Environmental responsibility:

www.axis.com/environmental-responsibility