

## AXIS P3225-LVE Mk II Network Camera

Streamlined, outdoor-ready HDTV 1080p fixed dome for any light conditions

AXIS P3225-LVE Mk II is a streamlined, outdoor-ready fixed dome that provides HDTV 1080p video. It features a varifocal lens and remote zoom and focus, which eliminates the need for hands-on fine tuning. Equipped with WDR – Forensic Capture to handle scenes with strong variations in light, Lightfinder technology for exceptional light sensitivity, as well as built-in IR illumination with OptimizedIR, this versatile camera provides outstanding video quality in any light conditions. It supports Axis Zipstream technology that significantly reduces bandwidth and storage requirements. The vandal-resistant AXIS P3225-LVE Mk II is IK10 rated.

- > [HDTV 1080p video quality](#)
- > [Outdoor ready and IK10 rated](#)
- > [Lightfinder and WDR – Forensic Capture](#)
- > [OptimizedIR illumination](#)
- > [Axis Zipstream](#)



# AXIS P3225-LVE Mk II Network Camera

Camera		Data streaming	Event data
Image sensor	Progressive scan RGB CMOS 1/3"	Built-in installation aids	Remote zoom, Remote focus, Pixel counter, OptimizedIR with adjustable IR illumination intensity
Lens	Varifocal, 3.0–10.5 mm, F1.4 Horizontal field of view 92°–34° Vertical field of view 50°–20° Remote focus and zoom, P-Iris control, IR corrected	General	
Day and night	Automatically removable infrared-cut filter	Casing	IP66- and NEMA 4X-rated, IK10 impact-resistant casing with dehumidifying membrane Encapsulated electronics and captive screws Color: white NCS S 1002-B For repainting instructions of skin cover or casing and impact on warranty, contact your Axis partner.
Minimum illumination	HDTV 1080p 25/30 fps with WDR – forensic capture and Lightfinder: Color: 0.16 lux, F1.4 B/W: 0.03 lux, F1.4, 0 lux with IR illumination on HDTV 1080p 50/60 fps: Color: 0.32 lux, F1.4 B/W: 0.06 lux, F1.4, 0 lux with IR illumination on	Sustainability	PVC free
Shutter time	1/66500 s to 1 s	Memory	512 MB RAM, 256 MB Flash
Camera angle adjustment	Pan ±180°, tilt -5 to +75°, rotation ±95°	Power	Power over Ethernet IEEE 802.3af/802.3at Type 1 Class 3, max 10.8 W, typical 7.3 W
Video		Connectors	RJ45 10BASE-T/100BASE-TX PoE
Video compression	H.264 Baseline, Main and High Profile (MPEG-4 Part 10/AVC) Motion JPEG	IR illumination	OptimizedIR with power-efficient, long-life 850 nm IR LEDs with adjustable illumination intensity. Range of reach up to 30 m (100 ft) depending on scene
Resolutions	1920x1080 to 160x90	Storage	Support for microSD/microSDHC/microSDXC card SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see <a href="http://www.axis.com">www.axis.com</a>
Frame rate	With WDR: 25/30 fps with power line frequency 50/60 Hz Without WDR: 50/60 fps with power line frequency 50/60 Hz	Operating conditions	-40 °C to 50 °C (-40 °F to 122 °F) Start-up: -30 °C to 50 °C (-22 °F to 122 °F) Humidity 10 to 100% RH (condensing)
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Axis Zipstream technology in H.264 Controllable frame rate and bandwidth, VBR/MBR H.264	Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)
Multi-view streaming	2 individually cropped out view areas	Approvals	EMC EN 55022 Class B, EN 61000-6-1, EN 61000-6-2, EN 55024, EN 50121-4, IEC 62236-4, FCC Part 15 Subpart B Class A and B, ICES-003 Class B, VCCI Class B, RCM AS/NZS CISPR 22 Class B, KCC KN22 Class B, KN24 Safety IEC/EN/UL 60950-1, IEC/EN/UL 60950-22, IEC/EN 62471 Environment IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-14 IEC 60068-2-6 (vibration), IEC 60068-2-27 (shock), IEC 60068-2-30, IEC 60068-2-78, IEC/EN 60529 IP66, NEMA 250 Type 4X, IEC/EN 62262 IK10
Pan/Tilt/Zoom	Digital PTZ, Preset positions	Dimensions	Height: 104 mm (4 1/16 in) ø 149 mm (5 7/8 in)
Image settings	Compression, Color, Brightness, Sharpness, Contrast, Local contrast, White balance, Exposure control (including automatic gain control), Exposure zones, Fine tuning of behavior at low light, WDR – forensic capture: Up to 120 dB depending on scene, Text and image overlay, Mirroring of images, Privacy masks Rotation: 0°, 90°, 180°, 270°, including Corridor Format	Weight	800 g (1.8 lb)
Network		Included accessories	Installation Guide, Windows decoder 1-user license, Mounting bracket, Cable gasket, Resistorx T20 L-key, Drill template, Connector guard
Security	Password protection, IP address filtering, HTTPS <sup>a</sup> encryption, IEEE 802.1X <sup>a</sup> network access control, Digest authentication, User access log, Centralized Certificate Management	Optional accessories	AXIS ACI Conduit Bracket A AXIS ACI Conduit Adapters AXIS T94M01L Recessed Mount Kit AXIS T94T01D Pendant Kit including weather shield AXIS Mounts Smoked dome
Supported protocols	IPv4/v6, HTTP, HTTPS <sup>a</sup> , SSL/TLS <sup>a</sup> , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP <sup>TM</sup> , SNMP v1/v2c/v3(MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH	Video management software	AXIS Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on <a href="http://www.axis.com/support/downloads">www.axis.com/support/downloads</a>
System integration		Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese
Application Programming Interface	Open API for software integration, including VAPIX <sup>®</sup> and AXIS Camera Application Platform; specifications at <a href="http://www.axis.com">www.axis.com</a> AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile S and ONVIF Profile G, specification at <a href="http://www.onvif.org">www.onvif.org</a>	Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see <a href="http://www.axis.com/warranty">www.axis.com/warranty</a>
Analytics	AXIS Video Motion Detection, active tampering alarm Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see <a href="http://www.axis.com/acap">www.axis.com/acap</a>	a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. ( <a href="http://www.openssl.org">www.openssl.org</a> ), and cryptographic software written by Eric Young ( <a href="mailto:ey@cryptsoft.com">ey@cryptsoft.com</a> ).	
Event triggers	Analytics, Edge storage events	Environmental responsibility:	
Event actions	File upload: FTP, SFTP, HTTP, HTTPS, network share and email Notification: email, HTTP, HTTPS, TCP and SNMP trap Video recording to edge storage Pre- and post-alarm video buffering Send video clip Overlay text IR illumination on/off	<a href="http://www.axis.com/environmental-responsibility">www.axis.com/environmental-responsibility</a>	