

AXIS P1425-LE Mk II Network Camera

Compact, cost-effective HDTV surveillance with OptimizedIR

With Lightfinder and WDR – Forensic Capture, the AXIS P1425–LE Mk II bullet camera provides excellent image quality in HDTV 1080p resolution, even in complex light conditions. Axis' OptimizedIR automatically illuminates any scene taking place in complete darkness. The camera features Corridor Format, pixel counter, remote focus and zoom, as well as P–Iris control – ensuring optimal depth of field, resolution, image contrast and clarity. The I/O port can be used for notification to an alarm panel or control of a relay. Axis' Zipstream technology significantly reduces bandwidth and storage requirements. The outdoor-ready camera comes with an adjustable weather shield.

- > Lightfinder and WDR Forensic Capture
- > Axis' Zipstream technology
- > HDTV 1080p at up to 60 fps
- > Built-in IR LEDs with OptimizedIR, 20 meters (66 feet)
- > I/O support and Edge Storage







AXIS P1425-LE Mk II Network Camera

Camera	Progressive seen CMOS 1/2 0"	
lmage sensor	Progressive scan CMOS 1/2.8"	
Lens	3–10.5 mm, F1.4 Horizontal field of view 93°–33°	Built
	Vertical field of view 50°-18°	insta
	Varifocal, Autofocus, Remote focus and zoom, P-Iris control, IR corrected	Data
Day and night	Automatically removable infrared-cut filter	Casi
Minimum illumination	Color: 0.16 lux at F1.4, 25/30 fps Color: 0.32 lux at F1.4, 50/60 fps	
mummation	B/W: 0.03 lux at F1.4, 35/30 fps	Sust
	B/W: 0.06 lux at F1.4, 50/60 fps 0 lux with IR illumination on	Men Pow
Shutter time	1/66500 s to 1 s	
Video		Con
Video .	H.264 High, Main and Baseline profiles (MPEG-4 Part 10/AVC)	
compression	Motion JPEG	IR iI
Resolutions	HDTV 1080p 25/30 fps (WDR): 1920x1080 to 160x90 HDTV 1080p 50/60 fps (no WDR): 1920x1080 to 160x90	
	Meets relevant parts of SMPTE 274M (HDTV 1080p)	Stora
Frame rate	Up to 50/60 fps (50/60 Hz, no WDR) in all resolutions	
Video streaming	Multiple, individually configurable streams in H.264 and	
	Motion JPEG Axis' Zipstream technology in H.264	Ope
	Controllable frame rate and bandwidth	cond
	VBR/MBR H.264	Stor
Image settings	Manual shutter time, Compression, Color, Brightness, Sharpness,	Cond Appr
	White balance, Exposure control, Exposure zones, Fine tuning of behavior at low light, Text and image overlay, Privacy masks,	
	IR illumination	
	Wide Dynamic Range - Forensic Capture: Up to 120 dB depending on scene, Mirroring of images	
	Rotation: 0°, 90°, 180°, 270°, including Corridor Format	
Pan/Tilt/Zoom	Digital PTZ	
Network		
Security	Password protection, IP address filtering, HTTPSa encryption,	Wei
	IEEE 802.1X ^a network access control, Digest authentication, User access log	
Supported	IPv4/v6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP,	Dim
protocols	CIFS/SMB, SMTP, Bonjour, UPnPTM, SNMP v1/v2c/v3 (MIB-II),	Inclu
	DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH	acce
System integro		Opti
Application Programming Interface	Open API for software integration, including VAPIX®	acce
	and AXIS Camera Application Platform; specifications at	
	www.axis.com ONVIF® Profiles S and G, specifications at www.onvif.org	
	·	
Analytics	AXIS Video Motion Detection 3	
Analytics	AXIS Video Motion Detection 3 Support for AXIS Camera Application Platform	Vide
Analytics	Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection,	
Analytics	Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see	man
·	Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection,	man soft
Analytics Event triggers	Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see www.axis.com/acap Analytics Detectors: Day/Night Mode, Live Stream Accessed, Tampering	soft Lang
·	Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see www.axis.com/acap Analytics Detectors: Day/Night Mode, Live Stream Accessed, Tampering Hardware: Network, Temperature	soft Lang
·	Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see www.axis.com/acap Analytics Detectors: Day/Night Mode, Live Stream Accessed, Tampering Hardware: Network, Temperature Input Signal: Manual Trigger, Virtual Inputs	Man soft Lang War
·	Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see www.axis.com/acap Analytics Detectors: Day/Night Mode, Live Stream Accessed, Tampering Hardware: Network, Temperature Input Signal: Manual Trigger, Virtual Inputs Storage: Disruption, Recording System: System Ready	Man Soft Lang War
Event triggers	Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see www.axis.com/acap Analytics Detectors: Day/Night Mode, Live Stream Accessed, Tampering Hardware: Network, Temperature Input Signal: Manual Trigger, Virtual Inputs Storage: Disruption, Recording System: System Ready Time: Use Schedule, Recurrences	War
·	Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see www.axis.com/acap Analytics Detectors: Day/Night Mode, Live Stream Accessed, Tampering Hardware: Network, Temperature Input Signal: Manual Trigger, Virtual Inputs Storage: Disruption, Recording System: System Ready Time: Use Schedule, Recurrences File upload: FTP, SFTP, HTTP, HTTPS network share and email	Vide man softs Lang War a. This
Event triggers	Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see www.axis.com/acap Analytics Detectors: Day/Night Mode, Live Stream Accessed, Tampering Hardware: Network, Temperature Input Signal: Manual Trigger, Virtual Inputs Storage: Disruption, Recording System: System Ready Time: Use Schedule, Recurrences	War a. This

	WDR mode PTZ control, Overlay text IR illumination
Built-in installation aids	Pixel counter, Remote zoom (3.5x optical), Remote focus
Data streaming	Event data
General	
Casing	IP66, IP67- and NEMA 4X-rated casing (polyester polycarbonate blend)
Sustainability	PVC free
Memory	512 MB RAM, 256 MB Flash
Power	Power over Ethernet IEEE 802.3af/802.3at Type 1 Class 3 Typical: 4.6 W, max 11 W
Connectors	RJ45 10BASE-T/100BASE-TX PoE I/O: 4-pin terminal block for 1 alarm input and 1 output
IR illumination	OptimizedIR, highly efficient LEDs with adjustable intensity and angle of illumination. Range up to 20 m (66 ft)
Storage	Support for microSD/microSDHC/microSDXC card Support for recording to dedicated network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com
Operating conditions	-30 °C to 50 °C (-22 °F to 122 °F) Humidity 10–100% RH (condensing)
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)
Approvals	EN 61000-6-1, EN 61000-6-2, EN 50121-4, IEC 62236-4, EN 50581, EN 55024, EN 55032 Class A, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, RCM AS/NZS CISPR 22 Class A, KCC KN-32 Class A, KN-35, IEC/EN/UL 60950-1, IEC/EN/UL 60950-22, IEC/EN 62471, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14, IEC 60068-2-27, IEC 60068-2-30, IEC 60068-2-78, IEC/EN 60529 IP66/IP67, IEC/EN 62262 IK08, NEMA 250 Type 4X, IEC 60825-1
Weight	With weather shield: 800 g (1.75 lb)
Dimensions	Ø132 x 260 mm (Ø5 3/16 x 10 1/4 in)
Included accessories	Mounting bracket, Drill template, Installation Guide, Windows decoder 1-user license AXIS Weather Shield L
Optional accessories	AXIS T94F01M J-Box/Gang Box Plate AXIS T91A47 Pole Mount AXIS T94P01B Corner Bracket AXIS T94F01P Conduit Back Box AXIS Weather Shield K Axis PoE Midspans For more accessories, see www.axis.com
Video management software	AXIS Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on www.axis.com/techsup/software
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese
Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty

 This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (http://www.openssl.org/), and cryptographic software written by Eric Young (eay@cryptsoft.com).

Environmental responsibility:

www.axis.com/environmental-responsibility

