

AXIS M3044–WV Network Camera

HDTV 720p fixed mini dome with wireless connection

The palm-sized AXIS M3044-WV is an affordably priced, vandal- and dust-resistant indoor HDTV 720p fixed mini dome. WDR ensures that details in both the dark and bright areas of a scene are visible. The camera connects to the network over wireless LAN or over Ethernet with an integrated RJ45 connector. The factory-focused camera can be mounted on walls or ceilings and with its 3-axis camera angle adjustment it can be easily leveled and directed in any direction. Axis' Corridor Format enables vertically oriented video streams. AXIS M3044-WV supports video analytics such as people counting.

- > Ultra-compact, vandal and dust-resistant design
- > HDTV 720p / 1 MP
- > Connects over wireless LAN or Ethernet
- > Axis' Zipstream technology for reduced bandwidth and storage
- > Axis' Corridor Format









General

AXIS M3044-WV Network Camera

Camera	
Image sensor	1/3" progressive scan RGB CMOS
Lens	M12 mount, Fixed iris, Fixed focus 2.8 mm, F2.0 Horizontal field of view: 82° Vertical field of view: 44°
Light sensitivity	0.25 lux at 50 IRE F2.0
Shutter time	1/32500 s to 1/5 s
Camera angle adjustment	Pan ±177°, Tilt ±76°, Rotation ±176° Can be directed in any direction and see the wall/ceiling
Video	
Video compression	H.264 (MPEG-4 Part 10/AVC), Main, Baseline and High Profiles, Motion JPEG
Resolutions	1280x720 (720p) to 320x240
Frame rate	25/30 fps with power line frequency 50/60 Hz
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG, Controllable frame rate and bandwidth, Axis' Zipstream technology in H.264, VBR/MBR H.264
Pan/Tilt/Zoom	Digital PTZ
Image settings	Compression, Color, Brightness, Sharpness, Contrast, White balance, Exposure control, WDR, Text and image overlay, Mirroring of images, Privacy mask Rotation: 0°, 90°, 180°, 270°, including Corridor Format
Network	
Wireless interface	Internal antenna IEEE 802.11 a/b/g/n, 2.4 and 5 GHz
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X ^a network access control, Digest authentication, Usa access log, Centralized Certificate Management WEP 64/128 bit, WPA/WPA2-PSK, WPA, WPA2 Enterprise WLAN pairing button (Wi-Fi Protected Setup TM PBC compatible)
Supported protocols	IPv4/v6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, SFTP CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMPv1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, TCP, UDP, IGMP, RTCP, ICMP, DHC ARP, SOCKS, SSH
System integro	rtion
Application Programming Interface	Open API for software integration, including VAPIX® and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile S, specification at www.onvif.org
Analytics	AXIS Video Motion Detection 3, Active tampering alarm Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection and third-party applications, see www.axis.com/acap
Event triggers	Analytics, Edge storage events
Event actions	File upload: FTP, SFTP, HTTP, HTTPS network share and email Notification: email, HTTP, HTTPS and TCP and SNMP trap Video recording to edge storage Send video clip Pre- and post-alarm video buffering Overlay text
Data streaming	Event data
Built-in installation aids	Pixel counter

Casing	Color: White NCS S 1002-B (For repainting of cover, remove the transparent dome. Contact your Axis partner for repainting instructions), Encapsulated electronics, Captive screws (Torx 10), IP42 water- and dust-resistant (to comply with IP42, follow Installation Guide), IK08 impact-resistant, polycarbonate/ABS casing
Sustainability	PVC free
Memory	512 MB RAM, 256 MB Flash
Power	4.8-5.2 V DC Typical 2.4 W, max. 2.7 W
Connectors	RJ45 10BASE-T/100BASE-TX Micro USB for DC power
Storage	Support for microSD/microSDHC/microSDXC card Support for recording to dedicated network-attached storage (NAS) For memory card and NAS recommendations see www.axis.com
Operating conditions	0 °C to 45 °C (32 °F to 113 °F) Humidity 15-85% RH (non-condensing)
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)
Approvals	EN 55032 Class B, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class A and B, ICES-003 Class B, , IEC/EN/UL 60950-1, EN 300328, EN 301489-1, EN 301489-17, EN 301893, FCC Part 15 Subpart C, FCC Part 15 Subpart E, RSS-247 IEC/EN 60529 IP42, IEC/EN 62262 Class IK08
Dimensions	Height: 56 mm (2.2 in) ø 101 mm (4.0 in)
Weight	170 g (0.38 lb)
Included accessories	Power supply, Installation Guide, Windows decoder 1-user license, Torx L-key
Optional accessories	AXIS T94B02D Pendant kit AXIS T94B02L Recessed mount AXIS T94B01P Conduit back box AXIS T94B02M J-Box/Gang box plate View protection Black casing Smoked dome Axis Mounts AXIS Surveillance microSDXC™ Card For more accessories see www.axis.com
Video management software	AXIS Camera Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on www.axis.com/techsup/software
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese
Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty

a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (http://www.openssl.org/), and cryptographic software written by Eric Young (eay@cryptsoft.com).

 ${\bf Environmental\ responsibility:}$

www.axis.com/environmental-responsibility

