

## **AXIS Q3617-VE Network Camera**

## Outstanding image quality with easy installation

Thanks to its 1/1.8" sensor and high-performance image processing, AXIS Q3617-VE supports Lightfinder and WDR - Forensic Capture with optimal image quality in difficult light conditions. It provides 4 MP at 30 fps with WDR, or 6 MP at 20 fps with WDR disabled. AXIS Q3617-VE offers a unique remote pan/tilt/roll/zoom (PTRZ) solution, easy conduit connection and cable management for minimized installation time. The PTRZ capability is also useful if the camera needs to be redirected. Robust and reliable, AXIS Q3615-VE is designed for harsh environments. Electronic image stabilization delivers steady images even during vibrations.

- > Exceptional video quality with 1/1.8" sensor
- > Lightfinder and WDR Forensic Capture
- > 4 MP at 30 fps with WDR
- > Unique PTRZ capability for efficient installation
- > Axis' Zipstream technology









## **AXIS Q3617-VE Network Camera**

Camera	
Image sensor	Progressive scan RGB CMOS 1/1.8"
Lens	Varifocal, 4.1–9 mm, F1.6 Horizontal field of view: 6 MP mode: 101°–46°, 4 MP 16:9 mode: 90°–41° Vertical field of view: 6 MP mode: 66°–30°, 4 MP 16:9 mode: 49°–23° Remote focus and zoom, P-Iris control, IR corrected
Day and night	Automatically removable infrared-cut filter
Minimum illumination	Color: 0.18 lux at 50 IRE, F1.6; B/W: 0.03 lux at 50 IRE, F1.6
Shutter time	1/100000 s to 2 s
Camera angle adjustment	Pan 370° Tilt +/- 81° Roll +/- 110°
Video	
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline, Main and High Profiles Motion JPEG
Resolutions	3072x2048 to 160x90
Frame rate	4 MP 16:9 (2720x1536) or 4:3 (2304x1728) with WDR: 25/30 fps with power line frequency 50/60 Hz 6 MP (3072x2048) without WDR: 20 fps
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Axis' Zipstream technology in H.264 Controllable frame rate and bandwidth VBR/MBR H.264
Multi-view streaming	Up to 4 individually cropped out view areas
Image settings	Compression, Color, Brightness, Sharpness, Contrast, White balance, Exposure control, Exposure zone, Noise reduction, Fine tuning of behavior at low light, Rotation: 0°, 90°, 180°, 270° including Corridor Format, Text and image overlay, Privacy mask, Mirroring of images, Electronic image stabilization, Barrel distortion correction  WDR – forensic capture: Up to 115 dB depending on scene
Pan/Tilt/Zoom	2.2x optical zoom and 2x digital zoom Digital PTZ Optical zoom and digital PTZ preset positions
Network	optical 20011 and digital 112 preset positions
Security	Password protection, IP address filtering, HTTPS <sup>a</sup> encryption, IEEE 802.1X <sup>a</sup> network access control, Digest authentication, Use access log, Centralized Certificate Management
Supported protocols	IPv4/v6, HTTP, HTTPS <sup>a</sup> , SSL/TLS <sup>a</sup> , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP <sup>TM</sup> , SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP DHCP, ARP, SOCKS, SSH
System integra	tion
Application Programming Interface	Open API for software integration, including VAPIX® and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile S, specification at www.onvif.org
Analytics	AXIS Video Motion Detection 3, Active tampering alarm Support for AXIS Camera Application Platform enabling installation of AXIS Perimeter Defender, AXIS Digital Autotrackin and third-party applications, see <a href="https://www.axis.com/acap">www.axis.com/acap</a>
Event triggers	Analytics, Edge storage events, Shock detection
Event actions	File upload: FTP, SFTP, HTTP, HTTPS network share and email Notification: email, HTTP, HTTPS and TCP Video recording to edge storage, Pre- and post-alarm video buffering, Zoom or digital PTZ preset, Overlay text, Send SNMP trap

Data streaming	Event data
Built-in installation aids	Pan/tilt/roll: Designed to withstand at least 200 full cycles, Autoroll, Remote zoom, Remote focus, Pixel counter
General	
Casing	IP66-, IP67-, IP6K9K- and NEMA 4X-rated, IK10 impact-resistant casing with polycarbonate dome, aluminum base and dehumidifying membrane Color: White NCS S 1002-B For repainting instructions of casing and impact on warranty, contact your Axis partner.
Sustainability	PVC free
Memory	1 GB RAM, 256 MB Flash
Power	Power over Ethernet (PoE) IEEE 802.3af/802.3at Type 1 Class 3 Typical 6.1 W, max 11.4 W
Connectors	RJ45 10BASE-T/100BASE-TX PoE
Storage	Support for microSD/microSDHC/microSDXC card Support for recording to dedicated network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com
Operating conditions	-40 °C to 60 °C (-40 °F to 140 °F) Humidity 10–100% RH (condensing)
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)
Approvals	EMC EN 55022 Class B, EN 50121-4, IEC 62236-4, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class B, ICES-003 Class B, VCCI Class B, RCM AS/NZS CISPR 22 Class B, KCC KN32 Class B, KN35 Safety IEC/EN/UL 60950-22 Environment IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14, IEC 60068-2-7, IEC 60068-2-78, IEC/EN 60529 IP66/67, ISO 20653 IP6K9K, NEMA 250 Type 4X, IEC/EN 62262 IK10
Dimensions	Depth: 166 mm (6 9/16 in) Depth with weather shield: 224 mm (8 13/16 in) ø 198 mm (7 13/16 in)
Weight	2.3 kg (5.1 lb) with weather shield
Included accessories	AXIS Connector Guard A, Safety hook wire, Installation Guide, Windows decoder 1-user license, Resistorx® L-key, Weather shield, Mounting bracket, Drill template, Cable gasket, Axis U-shape conduit adapter
Optional accessories	AXIS T94V01L Recessed Mount, AXIS T94V01D Pendant Kit, AXIS T98A17-VE Cabinets, Axis Pole Mounts, Axis Ceiling Mounts, Axis Wall Mounts, AXIS T90B Illuminators, AXIS ACI Conduit Adapter 3/4" NPS, AXIS Q36-VE Smoked Dome, AXIS Surveillance microSDXC™ Card For more accessories, see www.axis.com
Video management software	AXIS Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on www.axis.com/techsup/software
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese
Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty

 a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (www.openssl.org), and cryptographic software written by Eric Young (eay@cryptsoft.com).

Environmental responsibility:

www.axis.com/environmental-responsibility

