

## AXIS P1405-LE Mk II Network Camera

Compact, cost-effective HDTV surveillance with built-in IR

With Lightfinder and WDR – Forensic Capture, the AXIS P1405-LE Mk II bullet camera provides excellent image quality in HDTV 1080p resolution, even in complex light conditions. The built-in IR provides automatic illumination of a scene in complete darkness. AXIS P1405-LE Mk II supports Corridor Format for vertically oriented video stream of corridors, hallways or aisles. Furthermore, it features pixel counter, remote focus and zoom, as well as P-Iris control – ensuring optimal depth of field, resolution, image contrast and clarity. Axis' Zipstream technology significantly reduces bandwidth and storage requirements. The outdoor-ready camera comes with an adjustable weather shield.

- > [Lightfinder and WDR – Forensic Capture](#)
- > [Axis' Zipstream technology](#)
- > [HDTV 1080p at up to 30 fps](#)
- > [Built-in IR LED, 10 meters \(33 feet\)](#)
- > [Edge storage](#)



# AXIS P1405-LE Mk II Network Camera

<b>Camera</b>		WDR mode
<b>Image sensor</b>	Progressive scan CMOS 1/2.8"	PTZ control, Overlay text
<b>Lens</b>	2.8–10 mm, F1.6 Horizontal field of view 93°–32° Vertical field of view 51°–18° Varifocal, Autofocus, Remote focus and zoom, P-Iris control, IR corrected	IR illumination
<b>Day and night</b>	Automatically removable infrared-cut filter	<b>Built-in installation aids</b>
<b>Minimum illumination</b>	Color: 0.18 lux at F1.6 B/W: 0.04 lux at F1.6 0 lux with IR illumination on	Pixel counter, Remote zoom (3.5x optical), Remote focus
<b>Shutter time</b>	1/66500 s to 1 s	<b>Data streaming</b>
<b>Video</b>		Event data
<b>Video compression</b>	H.264 High, Main and Baseline profiles (MPEG-4 Part 10/AVC) Motion JPEG	<b>General</b>
<b>Resolutions</b>	HDTV 1080p 25/30 fps (WDR): 1920x1080 to 160x90 Meets relevant parts of SMPTE 274M (HDTV 1080p)	<b>Casing</b>
<b>Frame rate</b>	Up to 25/30 fps (50/60 Hz) in all resolutions	IP66, IP67- and NEMA 4X-rated casing (polyester polycarbonate blend)
<b>Video streaming</b>	Multiple, individually configurable streams in H.264 and Motion JPEG Axis' Zipstream technology in H.264 Controllable frame rate and bandwidth VBR/MBR H.264	<b>Sustainability</b>
<b>Image settings</b>	Manual shutter time, Compression, Color, Brightness, Sharpness, White balance, Exposure control, Exposure zones, Fine tuning of behavior at low light, Text and image overlay, Privacy masks, IR illumination Wide Dynamic Range - Forensic Capture: Up to 120 dB depending on scene, Mirroring of images Rotation: 0°, 90°, 180°, 270°, including Corridor Format	PVC free
<b>Pan/Tilt/Zoom</b>	Digital PTZ	<b>Memory</b>
<b>Network</b>		512 MB RAM, 256 MB Flash
<b>Security</b>	Password protection, IP address filtering, HTTPS <sup>9</sup> encryption, IEEE 802.1X <sup>9</sup> network access control, Digest authentication, User access log	<b>Power</b>
<b>Supported protocols</b>	IPv4/v6, HTTP, HTTPS <sup>9</sup> , SSL/TLS <sup>9</sup> , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP <sup>TM</sup> , SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH	Power over Ethernet IEEE 802.3af/802.3at Type 1 Class 3 Typical: 4.6 W, max 11 W
<b>System integration</b>		<b>Connectors</b>
<b>Application Programming Interface</b>	Open API for software integration, including VAPIX <sup>®</sup> and AXIS Camera Application Platform; specifications at <a href="http://www.axis.com">www.axis.com</a> ONVIF <sup>®</sup> Profiles S and G, specifications at <a href="http://www.onvif.org">www.onvif.org</a>	RJ45 10BASE-T/100BASE-TX PoE
<b>Analytics</b>	AXIS Video Motion Detection 3 Support for AXIS Camera Application Platform enabling installation of AXIS Cross Line Detection, AXIS Digital Autotracking and third-party applications, see <a href="http://www.axis.com/acap">www.axis.com/acap</a>	<b>IR illumination</b>
<b>Event triggers</b>	Analytics Detectors: Day/Night Mode, Live Stream Accessed, Tampering Hardware: Network, Temperature Input Signal: Manual Trigger, Virtual Inputs Storage: Disruption, Recording System: System Ready Time: Use Schedule, Recurrences	Built-in IR, highly efficient LED Range up to 10 m (33 ft)
<b>Event actions</b>	File upload: FTP, SFTP, HTTP, HTTPS network share and email Notification: email, HTTP, HTTPS and TCP and SNMP trap External output activation Video recording to edge storage Pre- and post-alarm video buffering	<b>Storage</b>
		Support for microSD/microSDHC/microSDXC card Support for recording to dedicated network-attached storage (NAS) For SD card and NAS recommendations see <a href="http://www.axis.com">www.axis.com</a>
		<b>Operating conditions</b>
		-10 °C to 50 °C (14 °F to 122 °F) Humidity 10–100% RH (condensing)
		<b>Storage conditions</b>
		-40 °C to 65 °C (-40 °F to 149 °F)
		<b>Approvals</b>
		EN 61000-6-1, EN 61000-6-2, EN 50121-4, IEC 62236-4, EN 50581, EN 55024, EN 55032 Class A, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, RCM AS/NZS CISPR 22 Class A, KCC KN-32 Class A, KN-35, IEC/EN/UL 60950-1, IEC/EN/UL 60950-22, IEC/EN 62471, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14, IEC 60068-2-27, IEC 60068-2-30, IEC 60068-2-78, IEC/EN 60529 IP66/IP67, IEC/EN 62262 IK08, NEMA 250 Type 4X, IEC 60825-1
		<b>Weight</b>
		With weather shield: 800 g (1.75 lb)
		<b>Dimensions</b>
		Ø132 x 260 mm (Ø5 3/16 x 10 1/4 in)
		<b>Included accessories</b>
		Mounting bracket, Drill template, Installation Guide, Windows decoder 1-user license AXIS Weather Shield L
		<b>Optional accessories</b>
		AXIS T94F01M J-Box/Gang Box Plate AXIS T91A47 Pole Mount AXIS T94P01B Corner Bracket AXIS T94F01P Conduit Back Box AXIS Weather Shield K Axis PoE Midspans For more accessories, see <a href="http://www.axis.com">www.axis.com</a>
		<b>Video management software</b>
		AXIS Companion, AXIS Camera Station, Video management software from Axis' Application Development Partners available on <a href="http://www.axis.com/techsup/software">www.axis.com/techsup/software</a>
		<b>Languages</b>
		English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese
		<b>Warranty</b>
		Axis 3-year warranty and AXIS Extended Warranty option, see <a href="http://www.axis.com/warranty">www.axis.com/warranty</a>
		a. <i>This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (<a href="http://www.openssl.org/">http://www.openssl.org/</a>), and cryptographic software written by Eric Young (<a href="mailto:ey@cryptsoft.com">ey@cryptsoft.com</a>).</i>
		<b>Environmental responsibility:</b> <a href="http://www.axis.com/environmental-responsibility">www.axis.com/environmental-responsibility</a>