



## Ring Terminal T&B Catalog Number:

**UPC Number:**

F72

**Status:**

78621081220


**Description:**

Active

Non-Insulated Large Brazed Seam Ring Terminal, Length 1.35 Inches, Width .60 Inches, Bolt Hole 5/16 Inch, Wire Range #4 AWG, Copper, Tin Plated, 200 Pack

### Features

These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.



### General

Insulation Type	Non-Insulated - Brazed Seam
Terminal Series	F
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	4
Stud Size	5/16

### Dimension Information

Stock Thickness	.07
A (inches)	1.35
B (inches)	.60
C (inches)	.49
M (inches)	1.06

### Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

### Tooling

Tool Charts	Available on Website
Application Tools	WT115A, TBM6, TBM6S, WT3185
Recommended Tool	TBM6S

### Packaging

T&B Order Multiple	200
T&B Inner Pack	200
Package in Units	2000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	1.69 lbs. per 100
Alternate Package Qty	F4-516

### Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

### Notes

Not available on Mylar Tape.

## Certifications

RoHS Compliance Yes

## Certifications



File Nbr:

E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)