XWP10A Explosion -Protected Pressure Washer Tank



Product Overview:

The XWP10A pressurised washer tank is designed specifically for use with XF, XT and XP Series explosion-protected camera stations where the integral washer pump has not been specified.

The XWP10A can be manually pressurised to 4 bar for a maximum head height of 20 meters and features an ATEX-approved solenoid release valve that can be Switched independently or via the telemetry receiver card contained within the camera station housing.

The Casing is constructed from 316L stainless steel for maximum corrosion protection optimised for use with cameras stations located in onshore, offshore, marine and heavy industrial environments.

The XWP10A pressurised washer tank can also be used with third party housings subject to compatibility.


Product features:

- ATEX Ex emb Approved
- IP67 ingress protected solenoid
- Suitable for use in zones 1, 2, 21 & 22
- Onshore, Offshore, Marine & Heavy Industrial Applications
- For Use With XF , XT & XP Series Camera Stations
- 316L Stainless Steel Case Construction
- 2 Switching Options: Independently (230 VAC, 110 VAC, 24 VAC or 24 VDC) Telemetry Receiver (24 VAC)
- Available for Use With Third Party Housings



Specifications	
General	
Application	Zones 1, 2, 21 and 22. Onshore, Offshore, Marine and Heavy Industrial
ATEX Certification (Solenoid Valve)	ATEX II 2 G Ex emb II T4, T5, T6 (with Terminal Box) KEMA 98ATEX2542X, IECEX KEM 08.002X
Part Number	XWP10A-24 XWP10A-24DC XWP10A-110 XWP10A-230
Ingress Protection Rating	Solenoid valve: IP67
Features	
Pressure Gauge	Standard
Capacity	10 litres
Head Height	Up to 20m at 4 Bar Pressure
Electrical	
Solenoid Voltage	24 VAC, 24 VDC, 115 VAC OR 230 VAC
Power Consumption	Max 10 Watts
Mechanical	
Construction	316L Stainless Steel
Mounting Options	Free Standing or Wall Mount
Cable Entry	2 X 40 mm Dia Entry Holes, side and bottom
Operating Temp	-20°C to +60°C
Weight	25Kg (Full)
Size	711 x 438 x 260 mm (H x W x D)

Dimensions and Fixing





Eaton Masons Road Stratford-upon-Avon Warwickshire CV37 9NB United Kingdom

T: +44 (0) 1789 775 775

© 2015 Eaton All Rights Reserved Printed in UK Publication No. DSOX0080EN/B December 2015

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

All specifications, dimensions, weights and tolerances are nominal (typical) and Eaton reserve the right to vary all data without prior notice. No liability is accepted for any consequence of use.