

# Ausrack Floor onyx

## 19 inch light duty network cabinets



- Suitable for housing networking equipment including patch panels, modems and routers.
- Load rating tested to AS62208-2006.
- Manufactured from SPCC rolled steel.
- Powdercoated textured matte black.

Comes standard with:

- Frame and 2 x removable side panels
- Front tempered tinted safety glass window door
- Key lockable front and rear steel door
- 4 x full height RU marked and notched mounting rail
- 4 x full height vertical cable management systems with snap cover and internal cable rings (800mm wide cabinets only)
- Fixed shelf or shelves (1 on 22RU, 2 on 32RU and 3 for all other heights)
- 6-way power rails
- Adjustable feet and braked castor kit
- Roof mounted fan unit (2-way for ≤ 600mm deep, 4-way for 800 / 960mm deep)



### ORDERING GUIDE

| Part Number | RU | Dimensions (mm) |              |              | Total Height | Weight (kg) |
|-------------|----|-----------------|--------------|--------------|--------------|-------------|
|             |    | Height*<br>(A)  | Width<br>(B) | Depth<br>(C) |              |             |
| ARFX6622U   | 22 | 1115            | 600          | 600          | 1185         | 61.0        |
| ARFX6822U   | 22 | 1115            | 600          | 800          | 1185         | 74.0        |
| ARFX6632U   | 32 | 1550            | 600          | 600          | 1620         | 80.0        |
| ARFX6832U   | 32 | 1550            | 600          | 800          | 1620         | 96.0        |
| ARFX6932U   | 32 | 1550            | 600          | 960          | 1620         | 106.0       |
| ARFX6642U   | 42 | 1995            | 600          | 600          | 2065         | 97.0        |
| ARFX6842U   | 42 | 1995            | 600          | 800          | 2065         | 105.0       |
| ARFX6942U   | 42 | 1995            | 600          | 960          | 2065         | 123.0       |
| ARFX6647U   | 47 | 2220            | 600          | 600          | 2290         | 109.0       |
| ARFX6847U   | 47 | 2220            | 600          | 800          | 2290         | 117.0       |
| ARFX6947U   | 47 | 2220            | 600          | 960          | 2290         | 137.0       |
| ARFX8942U   | 42 | 1995            | 800          | 960          | 2065         | 167.0       |
| ARFX8947U   | 47 | 2220            | 800          | 960          | 2290         | 179.0       |

\* Height does not include feet or castors

