

# P5000i Digital Analysis Microscope


Automated Fiber Inspection and Pass/Fail Analysis

The #1 cause for troubleshooting in optical networks is contaminated fiber connectors. To address this problem, the International Electrotechnical Commission (IEC) has developed a standard for acceptable fiber end-face quality. Yet certifying compliance to this standard can be a time-consuming, complex, and subjective procedure.

The P5000i is a digital handheld microscope that automatically inspects and certifies the end faces of fiber connectors according to industry standards and specifications. This digital microscope provides instant pass/fail results at the push of a button, eliminating subjective and time-consuming guesswork.

Compatible with multiple platforms, including T-BERD®/MTS-2000/4000/5800/6000A, 8000v2, HST-3000, Certifier40G, CellAdvisor JD720C, laptops, PCs, and Android mobile devices, the P5000i provides fast, repeatable analysis that easily integrates into existing test procedures. The world's leading manufacturers, installers, and service providers already rely on Viavi Solutions to certify their fiber connectors. Whether testing on the production line or in the field, the P5000i gives any technician that handles fiber the same capabilities in the palm of their hand.

# **Eliminate Guesswork with Objective Testing**



#### **Key Benefits**

- Inspect and certify fiber end-face quality at the push of a button, making your technicians instant fiber experts
- Ensure physical-layer performance by guaranteeing fiber connectivity meets industry standards
- Eliminate confusion with fast, easy, and objective testing
- Certify fiber end-face quality with your existing Viavi test platform or mobile device
- Let your technicians get it right the first time, drive best practices, improve quality of work, and optimize workflows
- Ensure lifetime connections and protect network investments by preventing damage to fiber components and equipment

#### **Key Features**

- Connects via USB with multiple devices including Viavi tools, laptops/PCs, and Android mobile devices
- Repeatable pass/fail analysis eliminates subjective guesswork from the measurement process
- User-selectable acceptance profiles allow certification to any acceptance criteria
- Includes FiberChekPRO™ software for analysis and reporting with laptops/PCs
- Automatic image centering ensures the fiber always appears in the center of the screen
- Detailed report generation to certify and document results
- Dual magnification (200X and 400X) functionality provides high-level and detailed inspection and analysis
- Magnification toggle button allows easy switching in both live and analysis views
- Accepts FBPT series tips for comprehensive support for all connector types used in today's network

## The World's Most Versatile Pass/Fail Analysis Solution

The P5000i works with Viavi solutions that users rely on daily for essential testing. This means that users can guarantee connector compliance to industry standards with a fast, repeatable analysis that easily integrates into their existing test procedures. It easily connects with Viavi test solutions and mobile devices via a simple USB connection.





Download FiberChekMOBILE to your Android device from the Google Play store.

## **Specifications**

General Technical (typical at 25°C)			
Weight	110 g (3.88 oz)		
Dimensions (w $\times$ h $\times$ d)	140 x 46 x 44 mm (5.5 x 1.8 x 1.7 in)		
Low mag field-of-view (FOV)	Horizontal: 740 μm Vertical: 550 μm		
High mag field-of-view (FOC)	Horizontal: 370 μm Vertical: 275 μm		
Live image	640 x 480 fps		
Connector	USB 2.0 (backwards compatible to USB 1.1)		
Cord length	183 cm (6 ft)		
Camera sensor	2560 x 1920, 1/2.5-in CMOS		
Particle size detection	<1 µm		
Light source	Blue LED, 100,000+ hour life		
Lighting technique	Coaxial		
Power source	USB Port		
Certification	CE		
Warranty	1 yr		

### **Ordering Information**

P5000i			
Description	Part Number		
P5000i Digital Analysis Probe with FiberChekPRO	FBP-P5000i		
Kit: P5000i with FiberChekPro, 4 inspection tips, case	FBP-SD101		
Kit: P5000i and MP-60 with FiberChekPro, 4 inspection tips, 2 UPP adapters, case	FIT-SD103		
Kit: P5000i and MP-80 with FiberChekPro, 4 inspection tips, 2 UPP adapters, case	FIT-SD113		
Kit: P5000i with FiberChekPro, 7 inspection tips, case	FBP-MTS-101		
Activation key: P5000i Android device compatibility*	SW-FCM-A1		
Included Items			
Stand-Alone Device (FBP-P5000i)			
P5000i Digital Analysis Microscope			
Soft bag for microscope and accessories			
Carrying case for tips			
Inspection tip (patch cord: 2.5 mm)			
FiberChekPRO software installation disk			
QuickStart manual			
Kits with 4 Inspection Tips			
Bulkhead: SC, LC			
Patch cords: 2.5 mm, 1.25 mm			
Kits with 7 Inspection Tips			
Bulkhead: SC, LC, FC, SC-APC			

Kits with an MP Series Optical Power Meter (OPM)		
MP series USB OPM		
2.5 mm UPP adapter (FITP-UPP25)		
1.25 mm UPP adapter (FITP-UPP12)		
FiberChekPRO software installation disk		
Quickstart manual		
USB cable extender		
Inspection Ports		

Viavi has over 300 tips, patch cords, and adapters available for inspecting different fiber optic connectors for a variety of different applications. This is not an all-inclusive list, but provides solutions for the most common connectors and applications. Please contact Viavi for more information.

_			
7	П.	n	-
		u	3

Description	Part Number
LC-APC bulkhead (for FBP probe	FBPT-LC-APC
FC bulkhead (for FBP probe)	FBPT-FC
FC-APC bulkhead (for FBP probe)	FBPT-FC-APC
SC-APC bulkhead (for FBP probe)	FBPT-SC-APC
MTP bulkhead long reach (for FBP probe)	FBPT-MTP-L
MTP-APC polish bulkhead long reach (for FBP probe)	FBPT-MTPA-L

#### **Patch Cords**

Universal 2.5 mm (for FBP probe)	FBPT-U25MA
Universal 1.25 mm (APC polish slip fit (for FBP probe)	FBPT-U12MA-

#### Adapters (for devices with a dedicated patch cord microscope)

Universal 2.5 mm APC female threaded	FMAE-UAPC
LC duplex female threaded	FMAE-LC-2X
LC-APC female threaded	FMAE-LCA
MTP	FMAE-MTP
MTP APC polish	FMAE-MTPA

The activation key enables Android compatibility for both new P5000i orders and existing devices in the field. When purchased with a new product, the P5000i will ship pre-activated for Android compatibility. When purchased for activating an existing P5000i, the customer must provide the P5000i serial number with their order.

FiberChekMOBILE requires Android 4.1 operating systems or higher.

Many Android devices do not have a direct USB-A input port; connecting the P5000i (with a standard USB-A plug) may require a converter cable or hub to interface with the



Contact Us

**+1 844 GO VIAVI** (+1 844 468 4284)

To reach the Viavi office nearest you, visit viavisolutions.com/contacts.

© 2015 Viavi Solutions, Inc. Product specifications and descriptions in this document are subject to change without notice. p5000i-ds-fit-tm-ae 30168437 901 0114