

1701S6 Multi-Conductor - Banana Peel® Jacketless Cables



For more Information
please call

1-800-Belden1



General Description:

CAT5e+ (350MHz), Six Banana Peeled Cables of 4-Bonded-Pair, U/UTP-Unshielded, Plenum-CMP, Premise Horizontal Cable, 24 AWG solid bare copper conductors, FEP insulation, Ripcord, Flamarrest® inner jacket (natural), no overall jacket.

Usage (Overall)

Suitable Applications: Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
24	24	Solid	BC - Bare Copper

Total Number of Conductors: 48

Insulation

Insulation Material:

Insulation Material
FEP - Fluorinated Ethylene Propylene

Inner Jacket

Inner Jacket Material:

Inner Jacket Trade Name	Inner Jacket Material	Nom. Dia. (in.)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	.195

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
Unjacketed

Overall Cable

Overall Cabling Fillers: Spline

Overall Cabling Color Code Chart:

Color
1/ONE
2/TWO
3/THREE
4/FOUR
5/FIVE
6/SIX

Overall Nominal Diameter: 0.600 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

1701S6 Multi-Conductor - Banana Peel® Jacketless Cables

Bulk Cable Weight:	148 lbs/1000 ft.
Max. Recommended Pulling Tension:	240 lbs.
Min. Bend Radius/Minor Axis:	0.500 in.
Min. Bend/Installation:	6 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	Individual Leg: NEMA WC-63.1 Category 5e, UL Verified to Category 5e

Applicable Patents:

Country

www.belden.com/p

Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	1700S6

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)

15

Maximum Capacitance Unbalance (pF/100 m):	66
---	----

Nominal Velocity of Propagation:

VP (%)

72

Maximum Delay:

Delay (ns/100 m)

510

Max. Delay Skew:

Delay Skew (ns/100 m)

25

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)

9

Max. Operating Voltage - UL:

Voltage

300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.0	65.3	65.3	63.3	63.3	20.0
4	4.0	56.3	56.3	52.3	52.3	23.0
8	5.7	51.8	51.8	46.1	46.1	24.5

1701S6 Multi-Conductor - Banana Peel® Jacketless Cables

10	6.4	50.3	50.3	43.9	43.9	25.0
16	8.1	47.3	47.3	39.1	39.1	25.0
20	9.2	45.8	45.8	35.2	35.2	25.0
25	10.3	44.3	44.3	34.1	34.1	24.3
31.25	11.6	42.9	42.9	31.3	31.3	23.6
62.5	16.8	38.4	38.4	21.6	21.6	21.5
100	21.7	35.3	35.3	17.1	17.1	20.1
155	27.7	32.5	32.5	4.7	4.7	19.0
200	32.0	30.8	30.8	3.0	3.0	19.0
250	36.4	29.3	29.3	>0	>0	18.0
300	40.5	28.2	28.2			18.0
310	41.3	27.9	27.9			18.0
350	44.3	27.2	27.2			17.0

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 12	105 ± 10	63.8	60.8
4	100 ± 12	100 ± 10	51.7	48.8
8	100 ± 12	100 ± 10	45.7	42.7
10	100 ± 12	100 ± 10	43.8	40.8
16	100 ± 12	100 ± 10	39.7	36.7
20	100 ± 12	100 ± 10	37.7	34.7
25	100 ± 15	100 ± 10	35.8	32.8
31.25	100 ± 15	100 ± 10	33.9	30.9
62.5	100 ± 15	100 ± 10	27.8	24.9
100	100 ± 15	100 ± 10	23.8	20.8
155	100 ± 18	100 ± 10	19.9	16.9
200	100 ± 20	100 ± 10	17.7	14.7
250	100 ± 20	100 ± 10	15.8	12.8
300	100 ± 20	100 ± 10	14.2	11.2
310	100 ± 20	100 ± 10	13.9	10.9
350	100 ± 22	100 ± 10	12.9	9.9

Notes (Overall)

Notes: Belden IBDN. Bundled version of 1701A. Jacket sequentially marked at 2 ft. intervals. Individual Legs third party verified to TIA/EIA-568-B.2, Category 5e. Min Bend / Installation refers to individual subunit.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1701S6 D15X	1 FT	0.156 LB	BLUE	C	6X CAT5E CMP BANANA PEEL REEL
1701S6 D151000	1,000 FT	156.000 LB	BLUE	C	6X CAT5E CMP BANANA PEEL REEL
1701S6 D15500	500 FT	81.500 LB	BLUE	C	6X CAT5E CMP BANANA PEEL REEL

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 03-10-2014

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.