



AD200

Technical Data Sheet

Liquid Properties

Chemical Base	Ethyl Hybrid CA
Appearance:	Colourless liquid
Specific Gravity (25°C)	1.06 g/cm ³
Viscosity (25°C) [Cone & Plate]	1200 – 2200 mPa·s

Bonding Speed

Defined as the time taken to develop a strength of 0.1 N/mm² at 22°C and 50% relative humidity.

EPDM	<10 seconds
Neoprene	<10 seconds
Nitrile Rubber	<10 seconds
Balsa Wood	<15 seconds
Polycarbonate	10-20 seconds
Steel	25-40 seconds

Bonding Performance

Tensile strength according to ASTM D412 [B].


EPDM	>2.5 N/mm ²
Neoprene	>5 N/mm ²
Nitrile Rubber	>5 N/mm ²

Lap shear strength according to ISO 4587.

Steel	>14 N/mm ²
Aluminium	>8 N/mm ²
Nitrile Rubber	>2 N/mm ²
Polycarbonate	>3 N/mm ²


Temperature Resistance

Tested on mild steel, cured for 24-hours and conditioned to test temperature for 1 hour prior to pull test.



Enviro-Chemical Resistance

Exposed to conditions for 1,000 hours at 22°C except for 98% RH that had an exposure of 42°C.



Storage Conditions

Recommended Storage Temperature is 2-10 °C. Maximum storage temperature is 25°C. Shelf life at the recommended temperature (unopened) is 12 months.

HDPE containers do not offer a complete barrier, store product away from other chemicals and sources of humidity. Strong light exposure can discolour products.

Note:

The data contained herein are for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine the suitability for use in their specific application. We recommend that each user test their proposed application before repetitive use, this data sheet is merely a guide. We can accept no liability arising out of the use of this information of the products described herein.