


1752A Multi-Conductor - Enhanced Category 5e Bonded-Pair Patch Cable



For more Information
please call

1-800-Belden1

**General Description:**

CAT5e+ (350MHz), 4-Bonded-Pair, U/UTP-Unshielded, Tray - CM, Premise Patch Cable, 24 AWG Bonded Stranded (7x32) Tinned Copper Conductors, Polyolefin Insulation, PVC Jacket, RJ-45 Compatible

Usage (Overall)

Suitable Applications:

Premise Patch Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	7x32	TC - Tinned Copper, Bonded Strands

Total Number of Conductors:

8

Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
0.220

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
Bulk Cable Weight:	25 lbs/1000 ft.
Max. Recommended Pulling Tension:	40 lbs.
Min. Bend Radius/Minor Axis:	1 in.
Min. Bend/Installation:	2.200 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

CEC/C(UL) Specification:	CM
EU Directive 2011/65/EU (RoHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes

1752A Multi-Conductor - Enhanced Category 5e Bonded-Pair Patch Cable

EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	Category 5e - TIA 568.C.2
Other Specification:	ICEA 661, Cat 5e-100 Patch

Applicable Patents:

Country

www.belden.com/p

Flame Test

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT1

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Aerial:	No
Suitability - Burial:	No
Sunlight Resistance:	No

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)

15

Maximum Capacitance Unbalance (pF/100 m):	66
---	----

Nominal Velocity of Propagation:

VP (%)

70

Maximum Delay:

Delay (ns/100 m)

510

Max. Delay Skew:

Delay Skew (ns/100 m)

25

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)

9

Max. Operating Voltage - UL:

Voltage

300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.4	65.3	65.3	62.9	20.0
4	4.8	56.3	56.3	51.5	23.0
8	6.8	51.8	51.8	45.0	24.5
10	7.7	50.3	50.3	42.6	25.0
16	9.7	47.3	47.3	37.5	25.0
20	11.0	45.8	45.8	34.8	25.0
25	12.4	44.3	44.3	31.9	24.3
31.25	13.9	42.9	42.9	29.0	23.6
62.5	20.2	38.4	38.4	18.3	21.5

1752A Multi-Conductor - Enhanced Category 5e Bonded-Pair Patch Cable

100	26.0	35.3	35.3	9.2	20.1
155	33.2	32.5	32.5	0	19.0
200	38.4	30.8	30.8		19.0
250	43.7	29.3	29.3		18.0
300	48.6	28.2	28.2		18.0
310	49.5	27.9	27.9		18.0
350	53.2	27.2	27.2		17.0

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 12	105 ± 10	63.8	60.8
4	100 ± 12	100 ± 10	51.7	48.7
8	100 ± 12	100 ± 10	45.7	42.7
10	100 ± 12	100 ± 10	43.8	40.8
16	100 ± 12	100 ± 10	39.7	36.7
20	100 ± 12	100 ± 10	37.7	34.7
25	100 ± 15	100 ± 10	35.8	32.8
31.25	100 ± 15	100 ± 10	33.9	30.9
62.5	100 ± 15	100 ± 10	27.8	24.9
100	100 ± 15	100 ± 10	23.8	20.8
155	100 ± 18	100 ± 10	19.9	16.9
200	100 ± 20	100 ± 10	17.7	14.7
250	100 ± 20	100 ± 10	15.8	12.8
300	100 ± 20	100 ± 10	14.2	11.2
310	100 ± 20	100 ± 10	13.9	10.9
350	100 ± 22	100 ± 10	12.9	9.9

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft. intervals. Third party verified to ANSI/TIA-568-C.2, Category 5e Patch.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1752A F2VU1000	1,000 FT	23.000 LB	GRAY, DEC		CAT5E+ PATCH U/UTP CM BOX
1752A F2V1000	1,000 FT	25.000 LB	GRAY, DEC	C	CAT5E+ PATCH U/UTP CM REEL
1752A 002U1000	1,000 FT	23.000 LB	RED		CAT5E+ PATCH U/UTP CM BOX
1752A 002I1000	1,000 FT	25.000 LB	RED	C	CAT5E+ PATCH U/UTP CM REEL
1752A 003U1000	1,000 FT	23.000 LB	ORANGE		CAT5E+ PATCH U/UTP CM BOX
1752A 003I1000	1,000 FT	25.000 LB	ORANGE	C	CAT5E+ PATCH U/UTP CM REEL
1752A 004U1000	1,000 FT	23.000 LB	YELLOW		CAT5E+ PATCH U/UTP CM BOX
1752A 004I1000	1,000 FT	25.000 LB	YELLOW	C	CAT5E+ PATCH U/UTP CM REEL
1752A 005U1000	1,000 FT	23.000 LB	GREEN, DARK		CAT5E+ PATCH U/UTP CM BOX
1752A 005I1000	1,000 FT	25.000 LB	GREEN, DARK	C	CAT5E+ PATCH U/UTP CM REEL
1752A 006U1000	1,000 FT	23.000 LB	BLUE, LIGHT		CAT5E+ PATCH U/UTP CM BOX
1752A 006I1000	1,000 FT	25.000 LB	BLUE, LIGHT	C	CAT5E+ PATCH U/UTP CM REEL
1752A 007U1000	1,000 FT	23.000 LB	VIOLET		CAT5E+ PATCH U/UTP CM BOX
1752A 010U1000	1,000 FT	23.000 LB	BLACK		CAT5E+ PATCH U/UTP CM BOX
1752A 010I1000	1,000 FT	25.000 LB	BLACK	C	CAT5E+ PATCH U/UTP CM REEL

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 7 Revision Date: 07-27-2016

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).