

## A0270164 Faceplates and Panels - 250 PAIRS BIX MOUNT



For more Information  
please call

1-800-Belden1

**General Description:**

250 PAIRS BIX MOUNT

**Usage (Overall)**

Suitable Applications:	IBDN System 1200
Related Parts:	BIX CONNECTORS, DISTRIBUTION RING, MANAGEMENT MODULE, BIX PATCH COORD

**Physical Characteristics (Connectivity)****Capacity**

Max. Capacity:	250 PAIRS (10 connectors, 25 pairs)
----------------	-------------------------------------

**Access**

Front Connection:	Flush
Termination Area:	Front and Rear

**Dimensions****Dimensions:**

Height (in.)	Width (in.)	Depth (in.)
12.990	7.600	2.955

**Materials****Materials:**

Description	Material
Panel	Steel

**Color**

Color:	Beige
--------	-------

**Weight**

Weight:	2.600 lbs.
---------	------------

**Packaging**

Packaging:	Individually packaged in a cardboard box.
------------	---

**Mechanical Characteristics (Connectivity)**

Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C
Tool Compatibility:	BIX Connecting Tool (A0270165)

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/30/2008
Telecommunications Standards:	Category 5e - TIA 568.C.2
Safety Listing:	ACA, Bi-national Standard Listed

**Suitability**

Suitability - Indoor:	Yes
-----------------------	-----

**Transmission Characteristics (Connectivity)****Notes (Overall)**

**Notes:** For more information visit our web site at <http://www.belden.com>

**Product Family****Put Ups and Colors:**

**A0270164 Faceplates and Panels - 250 PAIRS BIX MOUNT**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
A0270164	1 EA	2.645 LB			BIX MOUNT 250-PAIR

Revision Number: 0    Revision Date: 03-27-2017

© 2017 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.