



SAFETY DATA SHEET

LAYOUT INK BLUE FLUID

Page: 1

Compilation date: 05/12/2014

Revision No: 6

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: LAYOUT INK BLUE FLUID

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Metal Marking Ink

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: STOT SE 3: H336; Aquatic Chronic 3: H412; Eye Irrit. 2: H319; Flam. Liq. 2: H225; -: EUH066

Most important adverse effects: Repeated exposure may cause skin dryness or cracking. Highly flammable liquid and vapour. Causes serious eye irritation. May cause drowsiness or dizziness. Harmful to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: EUH066: Repeated exposure may cause skin dryness or cracking.

H225: Highly flammable liquid and vapour.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H412: Harmful to aquatic life with long lasting effects.

Hazard pictograms: GHS02: Flame

GHS07: Exclamation mark

[cont...]

SAFETY DATA SHEET

LAYOUT INK BLUE FLUID

Page: 2



Signal words: Danger

Precautionary statements: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P233: Keep container tightly closed.
P240: Ground/Bond container and receiving equipment.
P241: Use explosion-proof electrical/ventilating/lighting/.. equipment.
P243: Take precautionary measures against static discharge.
P261: Avoid breathing dust/fumes/gas/mist/vapours/spray.
P264: Wash thoroughly after handling.
P273: Avoid release to the environment.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P303+361+353: IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P312: Call a POISON CENTER/doctor//if you feel unwell.
P337+313: If eye irritation persists: Get medical advice/attention.
P403+233: Store in a well-ventilated place. Keep container tightly closed.

2.3. Other hazards

Other hazards: In use, may form flammable / explosive vapour-air mixture.

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

ACETONE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
200-662-2	67-64-1	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	50-70%

PROPAN-2-OL

EINECS	CAS	PBT / WEL	CLP Classification	Percent
200-661-7	67-63-0	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336	10-30%

[cont...]

SAFETY DATA SHEET

LAYOUT INK BLUE FLUID

Page: 3

BASIC BLUE 26

219-943-6	2580-56-5	-	Acute Tox. 4: H302; Eye Irrit. 2: H319; Aquatic Chronic 1: H410	<2%
-----------	-----------	---	--	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Alcohol resistant foam. Water spray. Carbon dioxide. Dry chemical powder. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Highly flammable. In combustion emits toxic fumes. Forms explosive air-vapour mixture. Vapour may travel considerable distance to source of ignition and flash back.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn

[cont...]

SAFETY DATA SHEET

LAYOUT INK BLUE FLUID

Page: 4

leaking containers leak-side up to prevent the escape of liquid. Eliminate all sources of ignition.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.
Do not handle in a confined space. Avoid the formation or spread of mists in the air.
Smoking is forbidden. Use non-sparking tools.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Prevent the build up of electrostatic charge in the immediate area.
Ensure lighting and electrical equipment are not a source of ignition.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

ACETONE

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	1210 mg/m3	3620 mg/m3	-	-

PROPAN-2-OL

UK	400 ppm, 999 mg/m3	500 ppm, 1250 mg/m3	-	-
----	--------------------	---------------------	---	---

DNEL/PNEC Values

DNEL / PNEC No data available.

[cont...]

SAFETY DATA SHEET

LAYOUT INK BLUE FLUID

Page: 5

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Gloves (solvent-resistant). Latex gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Environmental: Prevent from entering in public sewers or the immediate environment.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Blue

Odour: Alcoholic

Evaporation rate: Fast

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Insoluble

Also soluble in: Acetone.

Viscosity: Non-viscous

Boiling point/range°C: 56

Flash point°C: -18

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions. Stable at room temperature.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Hot surfaces. Sources of ignition. Flames.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

[cont...]

SAFETY DATA SHEET

LAYOUT INK BLUE FLUID

Page: 6

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

ACETONE

IVN	RAT	LD50	5500	mg/kg
ORL	MUS	LD50	3	gm/kg
ORL	RAT	LD50	5800	mg/kg

PROPAN-2-OL

IVN	RAT	LD50	1088	mg/kg
ORL	MUS	LD50	3600	mg/kg
ORL	RAT	LD50	5045	mg/kg
SCU	MUS	LDLO	6	gm/kg

BASIC BLUE 26

ORL	RAT	LD50	900	mg/kg
-----	-----	------	-----	-------

Relevant hazards for substance:

Hazard	Route	Basis
Serious eye damage/irritation	OPT	Hazardous: calculated
STOT-single exposure	-	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

12.1. Toxicity

[cont...]

SAFETY DATA SHEET

LAYOUT INK BLUE FLUID

Page: 7

Hazardous ingredients:

ACETONE

BLUEGILL (<i>Lepomis macrochirus</i>)	LC50	8300	mg/l
---	------	------	------

BASIC BLUE 26

TROUT	96H LC50	100	mg/l
-------	----------	-----	------

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Waste code number: 08 01 11

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1993

14.2. UN proper shipping name

Shipping name: FLAMMABLE LIQUID, N.O.S.
(contains acetone, propan-2-ol)

14.3. Transport hazard class(es)

Transport class: 3

[cont...]

SAFETY DATA SHEET

LAYOUT INK BLUE FLUID

Page: 8

14.4. Packing group

Packing group: II

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

Phrases used in s.2 and s.3: EUH066: Repeated exposure may cause skin dryness or cracking.

H225: Highly flammable liquid and vapour.

H302: Harmful if swallowed.

H319: Causes serious eye irritation.

H336: May cause drowsiness or dizziness.

H410: Very toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.