

DIW25 Multi-Conductor - Category 3 Nonbonded-Pair Cable

For more Information
please call

1-800-Belden1



General Description:

CAT3 (16MHz), DIW 25-Pair, U/UTP-Unshielded, Riser-CMR, Premise Backbone Cable, 24 AWG solid bare copper conductors, PVC insulation, Ripcord, PVC jacket

Usage (Overall)

Suitable Applications: Premise Backbone Cable

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
25	24	Solid	BC - Bare Copper

Total Number of Conductors: 50

Insulation

Insulation Material:

Insulation Material
PVC - Polyvinyl Chloride

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.380 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue
2	White/Orange
3	White/Green
4	White/Brown
5	White/Slate
6	Red/Blue
7	Red/Orange
8	Red/Green
9	Red/Brown
10	Red/Slate
11	Black/Blue
12	Black/Orange
13	Black/Green
14	Black/Brown
15	Black/Slate
16	Yellow/Blue
17	Yellow/Orange
18	Yellow/Green
19	Yellow/Brown
20	Yellow/Slate
21	Violet/Blue
22	Violet/Orange
23	Violet/Green
24	Violet/Brown
25	Violet/Slate

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +60°C

DIW25 Multi-Conductor - Category 3 Nonbonded-Pair Cable

UL Temperature Rating:	60°C
Bulk Cable Weight:	100 lbs/1000 ft.
Max. Recommended Pulling Tension:	150 lbs.
Min. Bend Radius/Minor Axis:	3.800 in.
Min. Bend/Installation:	3.800 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMR
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	08/19/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	Meets Category 3 transmission performance requirements for multi-pair backbone cables as specified by TIA/EIA 568 B-2, including power-sum NEXT

Flame Test

UL Flame Test:	UL1666 Riser
C(UL) Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	DPLN25

Electrical Characteristics (Overall)

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)

9.380

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

5.000

Electrical Characteristics-Premise (Overall)

Premise Cable Electricals:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. PSNEXT (dB)	Min. SRL (dB)	Fitted Imp. (Ohms)
.772	2.200	43		
1.0	2.600	41	12	100 +/- 15
4.0	5.600	32	12	100 +/- 15
8.0	8.500	28	12	100 +/- 15
10.0	9.700	26	12	100 +/- 15
16.0	13.100	23	10	100 +/- 15

Notes (Overall)

Notes: Jacket sequentially printed with dual footage and meter markings.

Reference (Overall)

Previous Part Number: 24501858

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
DIW25 2901000	1,000 FT	96.000 LB	BEIGE, LIGHT		CAT3 25PR U/UTP CMR REEL
DIW25 732CUT	1 FT	0.000	GRAY, LIGHT OLIVE		CAT3 25PR U/UTP CMR CUT
DIW25 7321000	1,000 FT	96.000 LB	GRAY, LIGHT OLIVE		CAT3 25PR U/UTP CMR REEL
DIW25 732500	500 FT	89.500 LB	GRAY, LIGHT OLIVE		CAT3 25PR U/UTP CMR REEL
DIW25 7325000	5,000 FT	115.000 LB	GRAY, LIGHT OLIVE		CAT3 25PR U/UTP CMR REEL

DIW25 Multi-Conductor - Category 3 Nonbonded-Pair Cable

Revision Number: 3 Revision Date: 08-14-2013

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.