

**2-599625-2****Indoor/Outdoor Fiber Optic Cable, loose tube, OM4, 2000 m, aqua**

Body Features

Cable Color	Aqua
Cable Construction	1 x 12
Bend Radius (Installation)	130.05 mm 5.12 in
Bend Radius (Long Term)	80.00 mm 3.15 in
Tensile Strength (Installation)	1249.95 N 281.00 lbf
Tensile Strength (Long Term)	650.00 N 146.13 lbf
Weight (Nominal)	48.0 kg/km

Configuration Features

Number of Fibers	12
------------------	----

Dimensions

Length	1999.994 m 6561.660 ft
Outside Diameter (Nominal)	6.40 mm 0.25 in

Industry Standards

Flammability Rating	ULSZH (Universal Low Smoke Zero Halogen)
---------------------	--

Operation/Application

Environment	Outdoor
-------------	---------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Cable
Fiber Type	OM4
Armoring	None
Cable Type	Fiber Optic
Fiber Cable Buffering	Loose tube, gel-filled
Fiber Diameter	50/125 µm
Fiber Specification	IEC 60794-1

Signal Characteristics

Attenuation, maximum (1300nm)	1.00 dB/km
Attenuation, maximum (850nm)	3.50 dB/km

2-599625-2

Usage Conditions

Installation Temperature Range	-5 – 50 °C
Operating Temperature Range	-20 – 70 °C -4 – 158 °F
Storage Temperature Range	-20 – 70 °C

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant