



760193789 | 360-iP-G2-1U-LC-FX

SYSTIMAX 360™ iPatch® G2 LC Fiber Shelf, fixed

Construction Materials

Fiber Type	LazrSPEED® 150, 50 µm multimode fiber (OM2+) LazrSPEED® 300, 50 µm multimode fiber (OM3) LazrSPEED® 550, 50 µm multimode fiber (OM4) OptiSPEED®, 62.5 µm multimode fiber (OM1) TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1 or G.652.D, G.657.A1 OS2)
Material Type	ABS Polycarbonate

Dimensions

Depth	323.85 mm 12.75 in
Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in
Weight	1.81 kg 4.00 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	CE cUL UL ACMA
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Intelligence Type	iPatch® enabled
Product Type	Shelf
Shelf Movement	Fixed
Body Style	Duplex
Color	Black
Interface	LC
Package Quantity	1
Total Ports, quantity	24

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

