


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FLAT CLEANING SURFACE

PANDUIT PART NUMBER	DESCRIPTION
FMTPFCT	MPO/MTP FEMALE REEL CLEANING TOOL
APPROXIMATE PRODUCT DIMENSIONS	
3.2 X 5.0 X 1.4 inches [81 X 127 X 36 mm]	

NOTES:

1. THIS PRODUCT CLEANS SINGLEMODE AND MULTIMODE FERRULE ENDFACES OF MPO/MTP CONNECTORS WITHOUT GUIDE PINS (NOT INSTALLED IN A MPO/MTP ADAPTER).
2. THE PRODUCT HOUSING INCORPORATES AN ANTI-STATIC AGENT.
3. THE PRODUCT DESIGN ALLOWS FOR ONE-HANDED USE.
 - A. DEPRESSING A LEVER ON THE CLEANING TOOL OPENS THE PROTECTIVE SHUTTER, ADVANCES, AND EXPOSES A FRESH PORTION OF CLEANING CLOTH. RELEASING THE LEVER CLOSES THE SHUTTER.
 - B. WIPING THE FERRULE ENDFACE ON THE EXPOSED CLEANING CLOTH IN A SPECIFIED DIRECTION CLEANS THE CONNECTOR FERRULE ENDFACE.
4. THE CLEANING CLOTH:
 - A. IS AN ULTRA CLEAN MICRO-FIBER CLOTH THAT CAPTURES DEBRIS AND OTHER CONTAMINATION, DOES NOT FRAY, AND DOES NOT LEAVE ANY FIBROUS MATERIALS ON THE FERRULE ENDFACES BEING CLEANED.
 - B. PROVIDES APPROXIMATELY 400 CLEANINGS.
 - C. DOES NOT REQUIRE THE USE OF ADDITIONAL WET CLEANING AGENTS.
 - D. ALLOWS FOR USER REPLACEMENT OF CLEANING REEL.
5. OPERATING TEMPERATURE: 0 TO 40 °C
6. STORAGE TEMPERATURE: -20 TO 60 °C

PART NUMBER		FMTPFCT	
TITLE		MPT/MTP FEMALE REEL CLEANING TOOL	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		M01893ZN/00	
MATERIAL:		PANDUIT	
DRAWING NUMBER:		01893-56	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		THIRD ANGLE PROJECTION	
DRAWN BY		DATE	
MC		12-11-06	
CHK		SCALE	
MMW		NONE	
SHT 1 OF 1		A	

1	6/11/15	JSP	WJM	JGSW	A. REVISED DRAWING TITLE BLOCK.	01893-56
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

2

1

B

A

A

A