


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT	FERRULE TYPE
FSCM2.0** FSCS2.0BU	.090 LBS/10 PCS. (40.8 G/10 PCS.)	ZIRCONIA (CERAMIC)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. MULTIMODE CONNECTORS (FSCM2.0**) ACCEPT 50/125 OR 62.5/125 μ m MULTIMODE GLASS OPTICAL FIBER.
3. SINGLEMODE CONNECTORS (FSCS2.0BU) ACCEPT 9/125 μ m SINGLEMODE GLASS OPTICAL FIBER.
4. COMPLIES WITH THE FIBER OPTIC PERFORMANCE REQUIREMENTS AS SPECIFIED IN TIA/EIA 568-A AND B.3.
5. COMPLIES WITH FOCIS-3 (TIA/EIA 604-3).
6. DIMENSIONS IN [] ARE METRIC.

PART NUMBER		FSCM2.0**, FSCS2.0BU	
TITLE		FIBER OPTIC SC CONNECTOR	
CUSTOMER DRAWING			
ITEM REVISION NAME		M01069AD/00	
DATASET FILE NAME		M01069AD_DC/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ±		.XXX ± ANGLES ±	
		THIRD ANGLE PROJECTION	
DRAWN BY		DATE	
JH		05/23/06	
CHK		WMA	
SCALE		NONE	
DRAWING NUMBER:		01069-20	
SHT 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	12/8/15	JSP	WJM	JGSW	A. UPDATED DRAWING TITLE BLOCK.	01069-20