

# EDGE™ Reverse Polarity Uniboot Duplex Jumper

Bend-improved single-mode (OS2), 3 m

CORNING

EDGE™ Reverse Polarity Uniboot Duplex Jumpers allow for the quick and easy conversion from a TIA-568 A-B polarity to a TIA-568 A-A polarity without exposing the fibres or needing any tools. This jumper comes with a straight-through polarity from the factory but you can convert it to a flipped jumper. This uniboot design allows one cable to carry both fibres, reducing the jumper bulk when routing.

## Features and Benefits

### Factory-terminated solutions

Provide consistent quality, ensure system performance, and reduce installation time

### Low insertion loss performance

Allows for more connections in a link when deploying a TIA-942-compliant system



## Specifications

### General Specifications

Application	Data Centre, Vertical Riser, General building applications
Cable type	Interconnect
Flame rating	Riser (OFNR)
Cable assembly type	Two Fibre
Fibre Category	Bend-improved SM (OS2)

### Design - Connector A

Connector Type	LC Uniboot
Ferrule Material	Ceramic
Housing material	Composite
Housing Colour	Blue
Boot colour	Blue

### Optical Specifications - Connector A

Polish	UPC
--------	-----

# EDGE™ Reverse Polarity Uniboot Duplex Jumper

Bend-improved single-mode (OS2), 3 m

CORNING

## Design - Connector B

Connector Type	LC Uniboot
Ferrule Material	Ceramic
Housing material	Composite
Housing Colour	Blue
Boot colour	Blue

## Optical Specifications - Connector B

Polish	UPC
--------	-----

## Cable design

Fibre Count	2
Outer jacket colour	yellow

## Mechanical Characteristics Cable

Nominal Outer Diameter	2 mm (0.08 in)
------------------------	----------------

## Mechanical Characteristics - Furcation Leg

Minimum Bend Radius	10 mm
---------------------	-------

## Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

## Ordering Information

Part Number	787802GD120003M
Product Description	EDGE™ Solutions Jumper, 2 fibres, LC Uniboot to LC Uniboot, Interconnect Cable, Riser, Bend-Improved Single-mode (OS2), 3 m
EAN Code	4056418172316
Length	3 m

# EDGE™ Reverse Polarity Uniboot Duplex Jumper

Bend-improved single-mode (OS2), 3 m

CORNING

## Shipping Information

Units Per Delivery

1/1



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.