




16A model :	Fuse	MCB
ATS-H8C13-16A_EN/3B-1	-	1



Input Rating : 16A, 200 ~ 230V
Inlet : 16A IEC60309 2P+E plug x 2
Cordset : 3 meter 1.5mm sq. H05V V-F cordset x 2
Protection : 16A hydraulic MCB x 1
Circuit Details : Output 16A max. C 13 # 1 - 8

16A model :	Fuse	MCB
ATS-H8C13-16A_C20/3B-1	-	1



Input Rating : 16A, 200 ~ 230V
Inlet : 16A IEC320 C20 plug x 2
Cordset : 3 meter 1.5mm sq. H05V V-F cordset x 2
Protection : 16A hydraulic MCB x 1
Circuit Details : Output 16A max. C 13 # 1 - 8

10A model :	Fuse	MCB
ATS-H8C13-10A_C14/3B-1	-	1



Input Rating : 10A, 200 ~ 230V
Inlet : 10A IEC320 C14 plug x 2
Cordset : 3 meter 1.5mm sq. H05V V-F cordset x 2
Protection : 10A hydraulic MCB x 1
Circuit Details : Output 10A max. C 13 # 1 - 8

Automatic transfer switch
Outlet : 10A Rated IEC320 C13 x 8

AUSTIN HUGHES
Design. Manufacturing. Global Services.

The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.
Copyright 2015 Austin Hughes Electronics Ltd. All rights reserved.

ATS Specification :
Local meter : 3-digital LED current meter
Nominal input voltage : 200 ~ 230V
Acceptable input voltage : ±10% nominal
Input frequency : 50 / 60Hz
Transfer time : 10 - 16ms typical
Electrical endurance : 1 x 10⁵ operations
Power consumption : Approx. 8VA

EMC	Compliance	: FCC & CE certified
Safety	Compliance	: CE / LVD certified
Environment	Compliance	: RoHS2 & REACH
Operating	Temperature	: -5 to 60 °C
Storage	Temperature	: -25 to 65 °C
Operating	Altitude	: 0 to 2,000 m
Storage	Altitude	: 0 to 15,000 m
Humidity		: 8 to 95% RH, non-condensing
Dimension		: 437.5 (W) x 270 (D) x 44.5 (H) mm
Material		: Steel
Color		: Black (chassis)