

126-00049

HellermannTyton



Article Number: 126-00049

Description: Wing Push Mount Tie, 6.0" Long, 50lb Tensile, PA66HIRHS, Black, 500/bag

Base Data		
	Local Order Number	126-00049
	Type	T50SSFM
	Color	Black (BK)
	Features and Benefits	• Wing design helps stabilize the tie in high vibration applications. • Includes a ladder type strap as opposed to a conventional serrated strap; giving the benefit of being extra flexible. • Wing design provides low insertion and high extraction force.
	Quantity Per	bag
	Product Description	Wing Push Mount Ties' supporting legs ensure a firm and secure fixing for bundles. These legs also reduce vibration in panel thickness enabling one part to suit many different applications such as sheet metal, wood, and cast iron.
	Short Description	Wing Push Mount Tie, 6.0" Long, 50lb Tensile, PA66HIRHS, Black, 500/bag
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225N
	Length L (Imperial)	6.3"
	Length L (Metric)	160.0mm
	Fixation Method	Arrowhead
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.18"
	Width W (Metric)	4.6mm
	Width W2 (Imperial)	0.6"
	Width W2 (Metric)	14.7mm
	Height H (Imperial)	0.2"

126-00049



Product Dimensions	Height H (Metric)	5.6mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	1.4"
	Bundle Diameter Max. (Metric)	35.0mm
	Panel Thickness Max. (Imperial)	0.12"
	Panel Thickness Max. (Metric)	3.0mm
	Panel Thickness Min. (Imperial)	0.03"
	Panel Thickness Min. (Metric)	0.7mm
	Mounting Hole Diameter D (Metric)	6.0 - 6.6 mm
	Mounting Hole Diameter D Min. (Imperial)	0.24"
	Mounting Hole Diameter D Max. (Imperial)	0.25"
	Mounting Hole Diameter D Max. (Metric)	6.6mm
	Mounting Hole Diameter D Min. (Metric)	6.0mm
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
	Material Shortcut	PA66HIRHS
	Flammability	UL94 HB
	Operating Temperature	-40°F to +230°F (-40°C to +110°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Metric)	500
	Customs Number(Schedule B)	3926909987