




## 14X12X6 HEATED & COOLED POE ENCLOSURE FOR 4 ELEMENT RPTNC EXTERNAL ANTENNA



The AccelTex Solutions Heated & Cooled PoE enclosure allows an access point to be installed in an outdoor or other temperature-limiting environment. The heater, fan and AP are all powered by a single PoE cable run from the network switch. The enclosure ships ready for an AP and external antenna installation.

**Part Number: ATS-14126-S-L-4T-CG-POE-HC**

### > HEATED & COOLED ENCLOSURE SYSTEM COMPONENTS

- 14x12x6 Poly Enclosure with Solid Door, Latch Lock, Cord Grip and Mounting Feet
- 1 Gbps Ethernet Surge Suppression
- 50W Power Injector and PoE Splitter
- 15W Heater and 12V Brushless Fan
- Adjustable Thermostat
- Ethernet Cables (Internal Only, Customer provides Ethernet Cable to Enclosure)
- Ground Bar, Ground Lug and all Internal Components Pre-wired to this Ground
- T-Bar for AP Mounting
- DIN Rail
- 4 RPTNC Lightning Arrestors
- 4 RPTNC Jack to RPTNC Plug Cable Assemblies
- 4 Right Angle RPTNC Jack to RPTNC Plug Adapters

### > POWER INJECTOR SPECIFICATIONS

Protocol: 802.3at GigaBit PoE (supports 802.3af)  
Input Voltage: AC 90V-264V at 120V/230V  
Input Frequency: 47-63hz  
Input Current: 0.75A at 120V AC  
Inrush Current: 25A Max at 120 VAC  
Operation Temperature: -13 to 122°F (-25 to 50°C)

### > POE SPLITTER SPECIFICATIONS

Protocol: 802.3at GigaBit PoE (supports 802.3af)  
Input Voltage: DC 36V-60V  
Operation Temperature: -13 to 140°F (-25 to 60°C)

### > WARRANTY

1 Year Limited Warranty