

AR3140W

NetShelter SX Networking Enclosure expands Schneider Electric's superior IT enclosure line with improved support for high density networking applications. Integrated high density cable managers and improved cable access roof provide support for large cable bundles. When combined with the Side Airflow Duct Kit, the Networking Enclosure ensures complete isolation of cold intake and hot exhaust air for large switches and SAN directors.



Overview

Description	<![CDATA[NetShelter SX Networking Enclosure expands Schneider Electric's superior IT enclosure line with improved support for high density networking applications. Integrated high density cable managers and improved cable access roof provide support for large cable bundles. When combined with the Side Airflow Duct Kit, the Networking Enclosure ensures complete isolation of cold intake and hot exhaust air for large switches and SAN directors.]]>
Model Name	NetShelter SX 42U 750mm Wide x 1070mm Deep Networking Enclosure with Sides White
Includes	Baying hardware , Key(s) , Keyed-alike doors and side panels , Leveling feet , Mounting Hardware , Pre-installed casters , Side Panels , Vertical cable managers
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

Supported Hardware

Panel Size	0
Brightness	0 nits
Pixel Pitch	0.0
Display Colors	0
LCD Power Consumption	0 W

Physical

Net Weight	155.95 kg
Maximum Height	1991.0 mm
Maximum Width	750.0 mm
Maximum Depth	1070.0 mm

Shipping Weight	167.83 kg
Shipping Height	2118.0 mm
Shipping Width	851.0 mm
Shipping Depth	1219.0 mm
Minimum Mounting Depth	11.0
Maximum Mounting Depth	32.25
Rack Height	42 U
Color	White
Units per Pallet	0.0
Vertical Posts	16 gauge
Front Door	16 gauge
Rear Door	16 gauge
Roof	18 gauge
EIA Mounting Rails	14 gauge
Side Panels	18 gauge

Environmental

CFM	0
-----	---

Conformance

Approvals	UL 2416 , UL 60950-1
Standard warranty	5 year repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Other Environmental Compliance	China RoHS