


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NO.	WEIGHT
FLEX-CM12S	0.75 lbs (0.34 kg)
FLEX-CM18S	

NOTES:


- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN BRACKETS ARE METRIC.
- MATERIAL: GALVANNEALED STEEL
COLOR: BLACK
- INCLUDES 2 TRANSITION BUNDLING CLIPS.
(18 POSITION OR 12 POSITION CLIPS AVAILABLE)
- TRANSITION PANEL ATTACHES TO STANDARD EQUIPMENT MOUNTING RAILS OF RACK OR CABINET.
- MOUNTING HARDWARE INCLUDED.
- ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.





FRONT VIEW



LEFT SIDE VIEW



ISO VIEW
(12 POSITION BUNDLING CLIPS SHOWN)

							TITLE HD FLEX UNIVERSAL REAR CABLE MANAGER							
							CUSTOMER DRAWING							
							ITEM REVISION NAME 12F187JE/00							
							DATASET FILE NAME 12F187JE_DC/00A							
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±					PART NO. SEE TABLE		
							 THIRD ANGLE PROJECTION					DRAWING NUMBER: 12F187JE -DC		
00	01-13-15	SAT	BSN	TMK	RELEASED TO PRODUCTION	12F187JE-DC	DRAWN BY SAT		DATE 01-13-15	CHK BSN	SCALE 1:2	SHT 1 OF 1		SIZE A
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN								