

# MODEL 600WP SPECIFICATIONS




## ELECTRICAL SPECIFICATIONS

SUPPLY VOLTAGE: 12 OR 24 VOLTS DC  
CURRENT DRAW: 440 MA. @ 12 VDC, 260 MA. @ 24 VDC

## MECHANICAL SPECIFICATIONS

HOLDING FORCE: 600 POUNDS MINIMUM  
HOUSING: STAINLESS STEEL

## WIRING DIAGRAM




FOUR CONDUCTOR  
22 AWG




# ALARM CONTROLS CORPORATION

19 BRANDYWINE DRIVE P.O. BOX 280  
DEER PARK, NY 11729  
1 800 645-5538

# MODEL 600WP INSTALLATION TEMPLATE



POSITION 2 FOLD ON THIS DOTTED LINE



**ALARM CONTROLS CORPORATION**  
**DEER PARK, NEW YORK 11729**


# GATE LOCK INSTALLATION EXAMPLES

USE AM3370 BRACKET FOR MODEL 600WP

USE AM6370 BRACKET FOR MODEL 1200WP

CONSULT FACTORY FOR CUSTOM BRACKETS


TYPICAL SLIDING GATE  
INSTALLATION



ANGLE BRACKET  
ATTACHES  
ARMATURE TO  
MOVING SECTION  
OF GATE

ANGLE BRACKET  
ATTACHES  
MAGNET TO  
STATIONARY  
SECTION  
OF GATE

TYPICAL SWINGING GATE  
INSTALLATION



ADJUSTABLE  
Z BRACKET  
ATTACHES  
ARMATURE TO  
MOVING SECTION  
OF GATE

MAGNET  
MOUNTS ON  
STATIONARY  
SECTION  
OF GATE



## ALARM CONTROLS CORPORATION

19 BRANDYWINE DRIVE P.O. BOX 280

DEER PARK, NY 11729

1 800 645-5538