

TrilogyExit: Add audit trail to panic exits

Add Trilogy convenience, programming, flexibility and audit trail to panic exit devices from most major manufacturers



OUTSIDE:

Rugged, field-proven Trilogy digital lock.

INSIDE:

Existing panic exit device – Most major brands supported



Add Trilogy convenience, programming, flexibility and audit trail to panic exit devices from most major manufacturers

TrilogyExit

- Clutch Mechanism insures long life and durability
- Fingertip and/or Windows Programmable
- 2000 User Codes: Master, manager, supervisor and users
- Real Time Clock for up to 40,000 Event Time/Date-Stamped Audit Trail
- Up to 500 Lock/Unlock Schedules (with Time Zone Support)
- Rugged 12-Button Metal Keypad
- Non-Handed; Fully Field Reversible
- Adaptable to most major manufacturers of standard RIM and IC RIM Cylinders
- Supports most panic exit devices including: Von Duprin 99, Corbin ED5000 & Yale, Dorma 9300, Arrow 3800, Old Style Sargent, New Style Sargent, Precision 1100, Cal Royal 9800
- Battery operated; uses 5 AA batteries

Also available in prox model for added convenience and security. Includes all of the features above plus:

- Accepts most HID Proximity cards and keyfobs
- Users are individually programmed to use a card only, code only, or for highest security – both card and code
- Prox card data can be added to software by uploading from lock, by using AL-PRE or entering directly from computer using DL-WINDOWS software.

Also available in prox only model (ETPL)

Trilogy audit trail and programming

AL-IR1 Infrared Printer

- Prints the event log and user code with hand-held convenience.

AL-DTMIII Data Transfer Module

- Module used to transfer program data from the PC to the lock and receive Audit Trail from the lock. Can transfer program data for up to 200 locks.

AL-PRE

- Alarm Lock Prox Reader/Enroller (For Use With Prox Lock) Prox Card Reader/Enroller Enables instant, automatic enrollment of Prox Cards into DL-Windows (just tap the Prox Card/fob device to the unit's faceplate to enroll)! Supports all prox cards and prox keyfobs. Simultaneous card enrollment, downloading or lock polling – all on just one serial port. Replaces AL-PCI. 9V Battery operation (6 mos. to 1 year, typical).

DL-WINDOWS SOFTWARE

- Windows-format software used to create programming, manager, users and schedules, receive audit trail from lock, program the lock using PC or laptop, program the AL-DTMIII to program multiple locks and configure the AL-DTMIII to transfer data.
- Free download at www.alarmlock.com

AL-PCI2 (not shown)

- Interface cable interconnects lock and PC for data transfer. (AL-PCI also includes DL-WINDOWS CD)

AL-PCI2U, (shown) as above, with USB interface cable



Remote Release Kit

RR-TRILOGYKIT

- Remote release kit for all Trilogy Cylindrical models includes the RR-1BUTTON for desk mount applications and RR-RECEIVER which is designed to be installed inside the battery compartment next to the battery pack of any cylindrical Trilogy lock. The RRRECEIVER connects to the 2 white remote release wires inside the battery compartment and to the black and red battery pack wires to power the receiver. These kits will retro fit to any existing cylindrical Trilogy manufactured since 1994.



Choice of three Trilogy finishes



US3 Polished Brass



US26D Satin Chrome



US10B Duronodic

U.S. Handing options



00 Straight Lever



75 Regal Curved Lever



25 Turnpiece
50 Knob available on
DL1250/1350

Matching Trilogy & Networkx Keypad models, see pgs 14 & 17

Trilogy & Networkx ordering information

Cylindrical Trilogys

DL 27 00 WP IC /26D -Y

Model/Series:

- DL27 = DL2700 Series
- DL28 = DL2800 Series
- DL30 = DL3000 Series
- DL32 = DL3200 Series
- DL52 = DL5300 Series
- PDL30 = PDL3000 Series
- PDL53 = PDL5300 Series

Networkx Wireless:

- DL6100 PIN Series;
- PDL6100, 7100 PIN/Prox

Trim:

- 00 = Lever
- 75 = Regal Curved Lever

Exterior/Interior Use:

For Exterior use of DL2700 & DL3000 only, order WP for weatherproof use. All other models are weatherproof as standard.

Cylinder:

IC = Standard Interchangeable Core Prep for Best, Falcon, Arrow, KSP
(Note: No "IC" indicates standard K.O. cylinder.)

Finish:

- /3 = US3 Polished Brass
- /26D = US26D Satin Chrome
- /10B = Duronodic (Special Order)

Special Order IC Prep:

- Y = Yale
- M = Medeco
- R = Sargent
- C = Corbin/Russwin
- S = Schlage

Mortise Trilogys

DL 35 00 DB R /26D EX

Model & Series:

DL35 = Trilogy T3 Mortise Series

Networkx Wireless:

DL6500 PIN; PDL6500 PIN/Prox

Trim:

- 00 = Standard Lever
- 75 = Regal Curved Lever (U.S. Option Only)

Lock Body:

- DB = Dead Bolt
- CR = Class Room (U.S. Only)

Handing:

Your Door -	Order -
Left Handed	L
Right Handed	R
Left Hand Reverse Bevel	R
Right Hand Reverse Bevel	L

(Note: Trim is non-handed. Lock body is field reversible.)

Finish:

- /3 = US3 Polished Brass
- /26D = US26D Satin Chrome
- /10B = Duronodic (Special Order)

European Model Suffix

Not Used For U.S. Models
*Note: Standard Lever for U.S. Models is Straight Lever. Standard Lever for European Models is Curved Tubular Lever

Trilogy Narrow Style

DL1200/26D1

Model Type

- PDL – Prox/PIN
- DL – Digital PIN

Trilogy Series

- 12 – 2700 Series
- 13 – 3000 Series

Trim

- 00 = Lever
- 25 = Turnpiece
- 50 = Knob
- 75 = Regal lever

Finish

- /26D Satin Chrome
- /10B Duronodic
- /MS Metallic Silver
- /MB Metallic Bronze

Mechanical Dead Latch

- 1 – Supports Adams Rite: 4710, 4730, 4900 Series
- 2 – Supports Adams Rite: 4070, MS1850S, MS1850S-050, MS1950, MS1950-050
- 3 – KIT Includes Adams Rite 4900 with 1-1/8" backset, 628 & 313 faceplate
- 4 – KIT Includes Adams Rite 4900 with 1-1/2" backset, 628 & 313 faceplate

Trilogy Exit

ETPDL- 1 R/ 26D V99

Type:

- PDL = Digital with Prox
- PL = Prox Only
- DL = No Prox
- N = (suffix) Networkx Wireless

Door Thickness:

- 1 = 1 3/4" + 1/8"
- 2 = 2" to 2 3/4"
- 3 = 3" to 4"

Handle:

- R = Regal
- S = Straight

Finish:

- /3 = US3 Polished Brass
- /26D = US26D Satin Chrome
- /10B = Duronodic (Special Order)

OEM Trim

- V99 = Von Duprin 99
- C50 = Corbin ED5000 & Yale
- D93 = Dorma 9300
- A38 = Arrow 3800
- S88 = Old Style Sargent
- N58 = New Style Sargent
- P11 = Precision 1100
- CR8 = Cal Royal 9800

Control Locks & Special Application Models

DL6500	PDL6500	PDL7100	DL1200	DL1300	PDL1300	ETDL	ETPDL	ETDLN	ETPDN	DL1200ET	DL1300ET	PDL1300ET	DK3000	PDK3000	NETDKPAK	NETPDKPAK
Mortise 802.11 Ethernet	Mortise Prox 802.11 Ethernet	Cylindrical Prox 802.11 Ethernet	Narrow Stile	Narrow Stile	Narrow Stile Prox	For use w/ panic device	For use w/ panic device ,Prox	For use w/ panic device 802.11 Ethernet	For use w/ panic device ,Prox, 802.11 Ethernet	Narrow Stile For use w/ panic device	Narrow Stile For use w/ panic device	Narrow Stile For use w/ panic device, Prox	Standalone Keypad	Standalone Keypad, Prox	Keypad 802.11 Ethernet	Keypad, Prox 802.11 Ethernet
5,000	5,000	5,000	100	2000	2000	2000	2000	2000	2000	100	2000	2000	2000	2000	5,000	5,000
3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-5 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits	3-6 digits
Keypad /PC	Keypad /PC	Keypad /PC	Keypad	Keypad /PC	Keypad /PC	Keypad /PC	Keypad /PC	Keypad /PC	Keypad /PC	Keypad	Keypad /PC	Keypad /PC	Keypad /PC	Keypad /PC	Keypad /PC	Keypad /PC
All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button	All metal, 12 button
Straight or curved lever	Straight or curved lever	Straight or curved lever	Straight or curved lever, thumbturn or knob	Straight or curved lever, thumbturn or knob	Straight or curved lever, thumbturn or knob	Straight or curved lever	Straight or curved lever	Straight or curved lever	Straight or curved lever	Straight or curved lever, thumbturn or knob	Straight or curved lever, thumbturn or knob	Straight or curved lever, thumbturn or knob			Straight or curved lever	Straight or curved lever
35,000	35,000	35,000		40000	40000	40000	40000	35,000	35,000		40000	40000	40000	40000	35,000	35,000
500	500	500		500	500	500	500	500	500		500	500	500	500	500	500
	Prox HID	iClass HID Prox / 13.56MHz			Prox HID		Prox HID		Prox HID			Prox HID		Prox HID		Prox HID
Global lockdown	Global lockdown	Global lockdown						Global Lockdown	Global lockdown						Global lockdown	Global lockdown
Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard
Handed; Field Reversible	Handed; Field Reversible	Nonhanded	Nonhanded	Nonhanded	Nonhanded	Nonhanded.	Nonhanded.	Nonhanded.	Nonhanded.	Nonhanded	Nonhanded	Nonhanded			Nonhanded	Nonhanded
1-5/8 to 1-7/8"	1-5/8 to 1-7/8"	1-5/8 to 1-7/8" others upon request	1-3/4"	1-3/4"	1-3/4"	1-5/8 to 1-7/8" (others on request.)	1-5/8 to 1-7/8" (others on request.)	1-5/8 to 1-7/8" (others on request.)	1-5/8 to 1-7/8" (others on request.)	1-3/4"	1-3/4"	1-3/4"			1-5/8 to 1-7/8" others upon request	1-5/8 to 1-7/8" others upon request
2-3/4" (included)	2-3/4" (included)	2-3/4" (included) 2-3/8" opt.	31/32", 1-1/8", 1-1/2"	31/32", 1-1/8", 1-1/2"	31/32", 1-1/8", 1-1/2"					31/32", 1-1/8", 1-1/2"	31/32", 1-1/8", 1-1/2"	31/32", 1-1/8", 1-1/2"			2-3/4" (included) 2-3/8" opt.	2-3/4" (included) 2-3/8" opt.
Generic mortise cylinder, supplied.	Generic mortise cylinder, supplied.	Large key-in-knob, incld -or- IC Prep for Best/Falcon/Arrow (w/o cyld.)	Generic 1-1/4" mortise cylinder, supplied. 1-1/8", 1-1/4"1-3/8" supported	Generic 1-1/4" mortise cylinder, supplied. 1-1/8", 1-1/4"1-3/8" supported	Generic 1-1/4" mortise cylinder, supplied. 1-1/8", 1-1/4"1-3/8" supported	Generic Rim Cylinder, supplied. Other mfrs. Cylinder Adapters must be ordered separately.	Generic Rim Cylinder, supplied. Other mfrs. Cylinder Adapters must be ordered separately.	Generic Rim Cylinder, supplied. Other mfrs. Cylinder Adapters must be ordered separately.	Generic Rim Cylinder, supplied. Other mfrs. Cylinder Adapters must be ordered separately.	Generic 1-1/4" mortise cylinder, supplied. 1-1/8", 1-1/4"1-3/8" supported	Generic 1-1/4" mortise cylinder, supplied. 1-1/8", 1-1/4"1-3/8" supported	Generic 1-1/4" mortise cylinder, supplied. 1-1/8", 1-1/4"1-3/8" supported			Large key-in-knob, incld -or- IC Prep for Best/Falcon/Arrow (w/o cyld.)	Large key-in-knob, incld -or- IC Prep for Best/Falcon/Arrow (w/o cyld.)
		Yale, Medeco, Sargent, Corbin/ Russwin, Schlage	Yale, Medeco, Corbin/ Russwin, Schlage	Yale, Medeco, Corbin/ Russwin, Schlage	Yale, Medeco, Corbin/ Russwin, Schlage					Yale, Medeco, Corbin/ Russwin, Schlage	Yale, Medeco, Corbin/ Russwin, Schlage	Yale, Medeco, Corbin/ Russwin, Schlage			Yale, Medeco, Sargent, Corbin/ Russwin, Schlage	Yale, Medeco, Sargent, Corbin/ Russwin, Schlage
yes	yes	yes				yes	yes	yes	yes				yes	yes	yes	yes
4 C cells 5 years 500,000	4 C cells 5 years 500,000	4 C cells 5 years 500,000	2-3V Lithium, 100,000	2-3V Lithium, 80,000	2-3V Lithium, 65,000	5AA; 60000	5AA; 60000	4 C cells 5 years 500,000	4 C cells 5 years 500,000	2-3V Lithium, 100,000	2-3V Lithium, 80,000	2-3V Lithium, 65,000			4 C cells 5 years 500,000	4 C cells 5 years 500,000
3 Hr Fire Rated UL	3 Hr Fire Rated UL	BHMA Grade 1 Lockset; 3hr. Fire Rated UL											UL	UL	Pending	Pending
US26D, 10B	US26D, 10B	US26D, 10B	US10B, US26D, MS, MB	US10B, US26D, MS, MB	US10B, US26D, MS, MB	US26D, US3, 10B	US26D, US3, 10B	US26D, US3, 10B	US26D, US3, 10B	US10B, US26D, MS, MB	US10B, US26D, MS, MB	US10B, US26D, MS, MB	US10B, US26D, MS, MB	US10B, US26D, MS, MB	US26D, 10B	US26D, 10B