

AP9631

10/100BASE-T network management card 2 with environmental monitoring

Product availability : Stock - Normally stocked in distribution facility

Price* : 479.00 USD



Main

Range of product	APC
Product or component type	UPS network management cards

Complementary

Communication port protocol	HTTP HTTPS SMTP SNMP v1 SNMP v3 TCP/IP Telnet
Communication network type	10/100BASE-T RJ45
Color	Black
Product weight	0.2 lb(US) (0.09 kg)
Height	1.5 in (38 mm)
Width	4.76 in (121 mm)
Depth	4.49 in (114 mm)

Environment

Relative humidity	0...95 % operating 0...95 % storage
Operating altitude	0...9842.52 ft (0...3000 m)
Storage altitude	0...49212.6 ft (0...15000 m)
Ambient air temperature for operation	32...113 °F (0...45 °C)
Ambient air temperature for storage	23...113 °F (-5...45 °C)
Product certifications	AS/NZS 3548 (C-Tick) class A EN 55022 class A EN 55024

FCC part 15 class A
GOST
ICES-003
VCCI class A

Environmental characteristic	RoHS compliant
------------------------------	----------------

Ordering and shipping details

Category	09305 - INDUSTRIAL UPS
Discount Schedule	IUPS
Nbr. of units in pkg.	1
Package weight(Lbs)	0.75
Returnability	N
Country of origin	PH

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1015 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	2 years repair or replace
-----------------	---------------------------
