



Overview

Model Name	APC Smart-UPS SRT 10000VA 208V
Includes	CD with software , Documentation CD , Installation guide , Temperature Probe , USB cable , Warranty card , Web/SNMP Management Card
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Output Power Capacity	10.0 KW / 10.0 kVA
Max Configurable Power (Watts)	10.0 KW / 10.0 kVA
Nominal Output Voltage	208V
Output Voltage Distortion	Less than 2%
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Other Output Voltages	240V
Crest Factor	3 : 1
Crest Factor	Double Conversion Online
Waveform Type	Sine wave
Output Connections	(1) Hard Wire 3-wire (2PH + G) (Battery Backup) , (2) NEMA L6-30R (Battery Backup) , (4) NEMA L6-20R (Battery Backup)
Bypass	Internal Bypass (Automatic and Manual)

Input

Nominal Input Voltage	208V
Input Frequency	40 - 70 Hz (auto sensing)
Input Connections	Hard Wire 3-wire (2PH + G)
Input voltage range for main operations	160 - 275 V
Input voltage adjustable range for mains operation	100 - 275 (half load)V

Other Input Voltages	240
Maximum Input Current	0 A
Input Breaker Capacity	0 A

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	1.5 hour(s)
Replacement Battery	APCRBC140
RBC Quantity	2

Communications & Management

Interface Port(s)	RJ-45 10/100 Base-T , RJ-45 Serial , Smart-Slot , USB
Available SmartSlot®; Interface Quantity	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Surge energy rating	480 joules
---------------------	------------

Physical

Maximum Height	432.0 mm
Maximum Width	263.0 mm
Maximum Depth	715.0 mm
Rack Height	0 U
Net Weight	111.58 kg
Shipping Weight	126.55 kg
Shipping Height	461.0 mm
Shipping Width	600.0 mm
Shipping Depth	1000.0 mm
Master Carton Units	0.0
Master Carton Weight	0.0 lbs
Color	Black
Units per Pallet	1.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95% non-condensing %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95% non-condensing %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	55.000 dB
Online Thermal Dissipation	2490.000 BTU/hr
Protection Class	IP 20

Conformance

Approvals	CSA C22.2 No.107.3-05 , ENERGY STAR (USA) , FCC Part 15 Class A , NOM , UL 1778
Standard warranty	3 years repair or replace (excluding battery) and 2 years for battery

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant
Battery Notes	Battery Notes