



Building Entrance Terminals

INDOOR - 110 CONNECTOR SERIES - BET



1880ENA1/NSC-100

100 PAIR - INDOOR BET - 110/110 - NO COVER

Product Specifications


UL497 Primary Protector for Communication Circuits

NAFTA Country of Origin: CANADA - All Models are "Buy America Act" Approved.

These 16 AWG steel building entrance terminals feature an industry standard 110 - style connector for both the input and output terminals. Also included are multiple external and internal ground lugs. UL approved standard on all terminals. Standard 5-pin protection modules, available in gas tube, solid state and hybrid versions, can be purchased separately. Call for more detailed information on RDUP/RUS-listed units.

Features & Benefits

- 16 AWG Powder Coated Steel Construction
- Equipped with an Internal 26 AWG Fuse Link
- External Ground Connectors Accept 6 - 14 AWG Wire
- Industry Standard 5 Pin Design
- Exceeds UL497 Primary Protection Standards
- 110 Connector Accepts 22 - 26 AWG Wire



1880ENA1/NSC-100

Ordering Information

Model Number	Stock Code	Pair Count	Input	Output	Dimensions (H" x W" x D")	Weight (lbs)
1880ENA1/NSC-100	328028	100	110	110	14.5 x 10.75 x 5.45	12



Building Entrance Terminals

INDOOR - 110 CONNECTOR SERIES - BET




1880ENA1/NSC-100

100 PAIR - INDOOR BET - 110/110 - NO COVER

Physical Dimensions

UL497 Primary Protector for Communication Circuits

14.5 x 10.75 x 5.45
(H" x W" x D")



Notes

Installation:

Indoor Wall Mount

Previous Model Number : 1880ENA1/NSC-100G