

Introduction:
The Transtector ALPU-PTP-M is a solid state high-current high-speed data protection system ideal for 10/1000BT Gigabit communication networks. The ALPU-PTP-M is compatible for Motorola PTP Radios. When considering the need for lightning protection equipment, most fixed point to point radio manufacturers require the installation to include lightning protection equipment in accordance with their warranty and installation recommendations. A typical installation should include two Lightning Protection Units, one installed on the wall, tower or mast adjacent to the radio and one installed at the cable entry point of the building in which the network resides. To minimize the possibility of lightning damage, it is recommended that each PTP radio be fitted with an ALPU-PTP-M to protect from damage and the associated costs of replacing damaged radios and other connected equipment.

General Description:
The Transtector ALPU-PTP-M is ideal for protecting high speed 10/1000BT communications networks. The protection circuits utilize silicon avalanche diode technology. The protection circuit board is housed in an aluminum enclosure. The enclosure is an outdoor qualified NEMA 3R type with versatile mounting flanges. The ALPU-PTP-M features RJ45 protection circuits for gigabit Ethernet data (pins 1,2 & 3,6 & 4,5 & 7,8). The unit is intended to be wall mounted with an optional bracket available to allow a wide range of pole mount configurations. A dedicated ground point on the housing must be bonded to the nearest grounding system (or Master Ground bar) for proper surge protection functionality. The system wiring is installed with RJ-45 type connectors that can install directly into the chassis without having to cut or splice or route through awkward strain relief holes. The enclosure includes a built in cable retention feature for improved cable management using screw down clamps. In the unlikely event of surge protection self sacrifice, the protection elements will fail short to disrupt communication.

Electrical:
Connector Style: RJ45 Cat5 shielded 100 ohm
Data Rate: 1000 Mb/s
Maximum Continuous Operating Voltage(MCOV): 92 Vdc
If installed in a Hazardous Location; MCOV = 85 Vdc
Protected Pins: (1,2) (3,6) (4,5) & (7,8) pass through
Impedance: 85 to 115 ohms
Surge Suppression: 134 Vpeak @ 100 A, 10/1000 ms
Suppression Response Time: < 5 ns
Peak Surge Current: 100A @10/1000µS
Nominal Live Current: 1 Amp
Capacitance: <15pF

Environmental:
Operating/Storage Temperature: -40°C to +75°C
Relative Humidity: 95% (non-condensing)

Mechanical:
Weight: 0.8 lbs (0.36 kg)
Product Material: Die-Cast Aluminum

Applicable Industry Standards:
Bonding and Grounding: NEC 800.100 and 830.100
Surge Suppression: GR-1089-2006
10/100BT (Ethernet), 1000BT (Gigabit Ethernet) Communication Protocol: IEEE 802.3
Power over Ethernet Protocol: IEEE 802.3af

Approvals:
CE Mark Compliant
IEC/ANSI/UL/CSA 60950 Compliant
Hazardous Location Certifications: ETL Class I Div 2, Class I Zone 2, ATEX, IECEx (See Figure 1)

REVISIONS				
REV.	DESCRIPTION	ECN	DATE	APPROVED
D	REFER TO ECN	13360	08/13/15	KAD








Figure 1: Hazardous Locations



ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES: FRACTIONS=± 1/32 .XX=± .01 ANGLES=± 1 ° .XXX=± .005 MATERIAL NOTED THIRD-ANGLE PROJECTION 	DRAWN HMB	DATE 2/14/13	<div>TRANSTECTOR</div> <div>TITLE ALPU-PTP-M</div>			
	ENG APPD CAP	4/2/13				
	PRODUCT MGR MLH	6/24/13				
	MARKETING APPD LJ	6/27/13				
	PROJECT NO.					
NOTICE: THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF TRANSTECTOR SYSTEMS. ALL RIGHTS RESERVED.	CUSTOMER SPECIFICATION					
	SIZE B	CAGE 30992	PART NUMBER 1101-959			REV D
	SCALE 1:2	PROD CAT DST	DOCUMENT NAME 1101-959-C		SHEET 1 OF 1	

THESE COMMODITIES, TECHNOLOGY OR
SOFTWARE WERE EXPORTED FROM THE
UNITED STATES IN ACCORDANCE WITH THE
EXPORT ADMINISTRATION REGULATIONS.
DIVERSION CONTRARY TO U.S. LAW PROHIBITED.