

#### 1080p Surface Mount Outdoor Dome IP Camera DWC-MV72i28V

28.2

32.5



## Summary

MEGApix<sup>®</sup> 2.1MP network cameras provide real-time 1080p High Definition video at 30fps. Advanced technologies include 50ft Smart IR<sup>™</sup> and true Day/Night for clear images in challenging lighting conditions. A built-in Web-Server and user-friendly interface make these cameras easy to use. Power over Ethernet simplifies installation by providing both power and the network connection through a single cable. All cameras are ONVIF conformant, assuring their successful integration with other open platform video surveillance products. Housed in our attractive dome enclosure, these cameras provide the industry-leading benefits of MEGApix<sup>®</sup> technology at an affordable price.

### Features

- 2.1 Megapixel Image Sensor (1080p, 30fps)
- Real-time 1080p 30fps High Definition
- Dual Codecs (H.264, MJPEG) with Simultaneous Streaming
- 2.8mm Fixed Lens
- Smart IR™ with Intelligent Camera Sync. 50ft Range
- True Day/Night with Mechanical IR Cut Filter
- Auto Gain Control (AGC)
- Back Light Compensation (BLC)
- Auto White Balance (AWB)
- Motion Detection
- Web Server Built-in
- PoE and DC12V
- OnVIF Compliant, Profile S
- Water Proof Cabling
- IP67 Certified (Weather Resistant)

#### Accessories (Optional)



DWC-V7WM Wall Mount Bracket for Mini Outdoor Dome Camera



DWC-V7CM Ceiling Mount Bracket for Mini Outdoor Dome Camera







: www.digital-watchdog.com

## Specifications

Dimensions

(unit:mm[inch])

# Οηνιε

5 Year Warranty

IMAGE	
Image Sensor	1/2.7* 2.1M CMOS
Total Pixels	1930 x 1088
Minimum Scene Illumination	F2.0 (30IRE): 1.4 Lux [Color]
	F2.0 (30IRE): 0.00 Lux [B/W]
LENS	
Focal Length	2.8mm Lens, F2.0
Lens Type	Fixed Lens
IR Distance	50ft Smart IR™
Angle of View	109°
OPERATIONAL	
Shutter Mode	Auto
Shutter Speed	1/30(25)sec ~ 1/10,000sec
White Balance	Auto Indoor/Auto Outdoor/Push/Manual/Hold
Auto Gain Control	Max 64dB
Day and Night	Auto, Day, Night, Schedule
NETWORK	
LAN	802.3 Compliance 10/100 base T LAN
Video Compression Type	H.264, MJPEG
Resolution	1080p / D1 / VGA / CIF / QVGA
Frame Rate	1-30fps
Streaming Capability	Multi Streaming CBR/VBR (Controllable frame rate and Bandwidth)
IP	IPv4, IPv6
Protocol	ONVIF, TCP/IP, UDP/IP, RTP(UDP), RTP(TCP), RTSP, NTP, HTTP, DNS, DDNS, DHCP
Maximum User Access	4 Users
OnVIF Conformance	OnVIF Profile S
Web Viewer	Browser: Internet Explorer, Google Chrome, Firefox OS: Windows 7
ENVIRONMENTAL	
Operating Temperature	-10°C ~ 50°C (14°F ~ 122°F)
Operating Humidity	Less than 90% (Non-Condensing)
IP Rating	IP67
Other Certifications	FCC, CE, ROHS
ELECTRICAL	
Power Requirements	DC 12V, POE IEEE 802.3af Class 2
Power Consumption	LED Off: 1.9W, 155mA
	LED On: 3W, 250mA
MECHANICAL	
Material	Aluminum Die-casting
Dimensions	4.13 x 2.38 in (105 x 60.7mm)
Weight	0.95lbs (350g)



Copyright © Digital Watchdog. All rights reserved. Specifications and pricing are subject to change without notice.