

### Features

- **Weather-Resistant Flush-Mount Design, Type-3R**
- **Telephone Line Powered, (No Battery or External Power Required for Telephone Operation)**
- **Tactile CALL Pushbutton for Pre-programmed One-Button Dialing**
- **Standard or SMART Operation**
- **Auto Answer (with Silent Monitoring)**
- **(2) Programmable Auxiliary Outputs for Peripheral Equipment Control**
- **Operating Range of -20°C to +60°C**
- **Call Received When Lit L.E.D.**
- **Voice Annunciation Option**
- **Extreme Cold Weather Option (-40°C)**
- **3-Number Rollover**
- **UL/CSA 60950 Compliant**
- **FCC Part 68 Certified**
- **ADA Compliant**
- **Monitored by TMA (Telephone Management Application) Software**



GAI-Tronics' RED ALERT® Auto-dial Telephones are designed to provide clear and reliable communications in almost any environment. The Model 397-00xAD is considered to be Type-3R weatherproof compliant when installed in a GAI-Tronics surface-mount enclosure, free-standing stanchion, wall-mount stanchion or simply recessed into an existing wall.

The 397-00xAD RED ALERT® Auto-dial Telephones provides reliable two-way communications with the press of a single button and can be installed on any analog PSTN, PBX, PABX, or KSU network providing 24 V dc or 48 V dc line voltage with a minimum line current of 24 mA. **No external power is required for normal operation.**

The Model 397-00xAD is capable of providing two (2) auxiliary outputs for control of peripherals such as strobes, door/gate access, alarms, or lamps via local or remote activation. These outputs can be programmed for a variety of control parameters including remote DTMF activation. Each telephone can additionally be configured to automatically answer when called.

Each telephone is ADA compliant, with a "Call Received When Lit" L.E.D. providing visual indication that a call is active.

Although each of these telephones will function as a standard telephone, connecting a customer-provided, central computer equipped with GAI-Tronics' TMA (Telephone Management Application) software will allow them to operate in SMART (Self-Monitoring and Reporting Technology) mode. With TMA connected, each RED ALERT® telephone will be polled on a scheduled basis to report:

- **Line integrity**
- **Microprocessor health**
- **Stuck buttons**
- **Microphone integrity**
- **Speaker integrity**
- **Line interrupt (power failure)**
- **Low Battery (Voice Annunciation Option only)**

Additionally, each RED ALERT® Auto-dial Telephone is available with an Extreme Cold Weather option (to -40°C).

### Specifications

TMA compatibility profile type . . . . GTC SMART Hands-free

#### Electrical

Audio Output. . . . . 1 kHz tone @  $87 \pm 3$  dB SPL  
@ 1 meter with 40 mA loop current  
Battery Voltage (tip and ring) . . . . . 24 V dc or 48 V dc  
Phone line requirements . . . . . Loop start, central office  
(CO), or Analog station port (PBX, PABX, or KSU)  
Minimum loop current . . . . . 24 mA  
(35 mA recommended)  
(2) Auxiliary outputs (Isolated solid state switch) . . . . .  
48 V dc @ 125 mA  
28 V<sub>RMS</sub> ac @ 80 mA<sub>RMS</sub>  
Signaling . . . . . DTMF 100 ms tone  
Memory . . . . . Non-volatile EEPROM

#### Mechanical

Operating Temperature Range:  
Model 397-003AD: -40° F to +140° F (-40° C to +60° C)  
Model 397-001AD: -4° F to +140° F (-20° C to +60° C)  
Relative Humidity. . . . . to 95%, no condensation  
Construction:  
Panel . . . . . 14-gauge, type 304 brushed  
stainless steel  
Back box . . . . . 16-gauge cold-rolled steel with  
black polyurethane finish  
Dimensions:  
Panel. . . . . 12.0 H x 10.0 W inches  
(304.8 x 254.0 mm)  
Back box (depth from mounting surface). . . . 2.38 inches  
(60.5 mm)  
Panel cutout . . . . . 10.1 H x 8.43 W inches  
(255.57 x 214.12 mm)  
Weight. . . . . 6.5 lbs. (2.9kg)

#### Approval Standards

Safety of Information Technology Equipment: UL/CSA 60950  
Enclosures for Electrical Equipment . . . . . UL 50, Type 3R

#### 47 CFR Part 68

Certification Number . . . . . US: ADGTE05BGTC2010  
Ringer Equivalent Number . . . . . .5B  
Network connection (USOC) . . . . . RJ11

#### IC information (Canada)

IC Certification Number . . . . . 882B-GTC 2010  
Ringer Equivalent Number . . . . . .5B  
Connection Method . . . . . CA11A

### Model Chart

Model	Description
397-001AD	Weatherproof, Flush-mount, One-Button, Auto-dial Telephone
397-003AD	Weatherproof, Flush-mount, One-Button, Auto-dial Telephone with Extreme Cold Weather Option
12509-042	TMA Package (includes transceiver, security key, interface cables, and software CD); supports both analog and VoIP telephones
12509-043	TMA Expansion Kit (includes transceiver, interface cables, and software CD); required for adding an additional analog telephone line; supports both analog and VoIP telephones
233-001	Security Screwdriver