



REVISION	DATE	BY	DATE	BY
		DRAWN	15/10/30	WW
		CHEK'D		
		VERIF'D		


Confidential – Property of Siemens Industry, Inc.		
CUSTOMER		
ORDER NO.	DWG. NO.	
	3F3Y075D16	SH 1 OF 2

SIEMENS		CATALOG NO. 3F3Y075D16 SERIAL NO. SERIES H 75 kVA 60 Hz 3 PHASE 4.8 % IMP AT 170 °C			
150 °C RISE 30 °C AVG. AMBIENT 220 °C TEMP CLASS 40 °C MAX. AMBIENT PRIMARY (H1 H2 H3) 480V V 10 kV BIL SECONDARY(X0 X1 X2 X3) 208Y/120V V 10 kV BIL		WINDING MATERIAL AL ENCLOSURE TYPE 3R WEIGHT 550 LBS ENERGY EFFICIENCY EXCEEDS CSA DOE 10 CFR PART 431:2016 SPACINGS BETWEEN ANY VENTILATED ENCLOSURE PANEL AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 5 INCHES EXCEPT WHEN WALL MOUNTED USING APPROVED WALL MOUNTING KIT		VOLTS 504 492 480 468 456 444 432 CONNECT 1 2 3 4 5 6 7	
SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION MANUAL NEMA Class ANN Dry Type Transformer		TYPE K  LISTED DRY TYPE TRANSFORMER 7705 E112313  LR 3902 SEISMIC QUALIFICATIONS, FLOOR MOUNT ONLY OSP-0136-10 IBC 2012/ASCE 7-10 SDS<=2.0g Z/h=1 Ip=1.5			

Siemens Industry, Inc. Norcross, GA



All Dimensions in inches



ENCLOSURE COLOR :ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #2/0-14 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR 600MCM-2 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential – Property of
Siemens Industry, Inc.

REVISION	DATE	BY	DATE	BY	CUSTOMER
			DRAWN 15/10/30	WW	
			CHEK'D		
			VERIF'D		
					ORDER NO.
					DWG. NO. 3F3Y075D16
					SH 2 OF 2

0.2 Jwen 2015/12/03 09:13