

GEMINI WIRELESS



Napco's crystal-control Gemini wireless products have been proven by an independent testing laboratory to outperform competitive products, with long-range RF reliability, as much as 50% higher than other top brands.

Gemini Transmitters range from keyfobs and panic buttons, to recessed door and surface-mount window/door contacts, to wireless PIR, PIR/pet and dual sensors, and from wireless smokes and glass breaks to heat detectors. Simply put, Gemini's uncommon crystal-control precision and omnidirectional circuitry, ensures the wireless/hardwire systems you provide your customers will dependably deliver the security and trouble-free, peace-of-mind they deserve for many years to come.

Advanced performance Gemini RF receivers

GEM-RECV-XP8 8 POINTS FOR EXPRESS, P801/800/P400 PANELS, ONLY

GEM-RECV-32 32 POINTS

GEM-RECV-96 96 POINTS

GEM-RECV-X255 255 POINTS

- > Dual diversity antennas minimize nulls & enhance reliability
- > Tamper- and RF-jamming supervision
- > Separate programmable supervisory times by device type
- > Audible fault-find mode in walk test
- > Also, fixed English language keypad GEM-K4RF with built in 32 pt receiver (see keypads section).



Low profile wireless window/door transmitter

GEM-TRANSLP

- > Ultra compact design, 2.5 x 1 x 0.4 (H x W x D inches)
- > Tamper supervised
- > Replaceable lithium PL2032 coin cell battery (supplied)
- > 5-year battery life, typical
- > Magnet and Internal reed switch
- > External lead (24" mini connector pigtail) for wiring external devices (jumper-selectable)
- > Magnet mounts with either supplied double-face tape or screws (screw tabs easily removable from mounting plate, at score)



Also in Brown **GEM-TRANSLP-BRN**

GEM-RTRANS (NOT SHOWN)

- > For recessed use in windows & doors



Wireless Carbon Monoxide Detector

GEMC-WL-CO

- > For use with Gemini & GEMC Comm'l Grade Receivers GEM-/GEMC-RECV
- > 5-3/8 diameter and approx. 2" profile, uses a 3V Lithium Battery (CR123A) for long life
- > Monitor alarms, restores, low battery, tamper and status
- > UL 2075, UL 2034



GEM-TRANSLP virtually disappears even in slimline window frames

How to build a winning Gemini System

Pick a panel



Gemini Panels

P816	P1632	P1664	P3200	P9600	X255	P801	GEM	
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	K1CA/DK1CA	STAY & AWAY
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	K1VPS	
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	K2AS	
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	K3DGTL/DK3DGTL	
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	K4RF	
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	K4	CLASSIC
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	RP1CAe2	
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	RP2ASe2	
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	RP3DGTL	
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	RP8LCD	
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	RP8/K800	

Gemini Keypads

Pick a keypad



GEM-DK1CA
INCLUDES 4 ZONE EXPANSION
MODULE BUILT-IN



GEM-K1VPS
(GEM1664, 1632 only)



GEM-RP3DGTL



GEM-K1CA
INCLUDES 4 ZONE EXPANSION
MODULE BUILT-IN



GEM-RP2ASe2



GEM-K3DGTL



GEM-RP1CAe2
INCLUDES 4 ZONE EXPANSION
MODULE BUILT-IN



GEM-K2AS



GEM-K4RF
WITH 32PT RF RECEIVER BUILT-IN FOR ALL
GEMINI EXPANDABLE PANELS



GEM-BIOREADER
OUTDOOR DIGITAL AND/OR
FINGERPRINT READER

Pick a wireless receiver

(Choose by # of wireless points)



32 PTS: GEM-REC32
96 PTS: GEM-REC96
255 PTS: GEM-REC255

Choose wireless devices



GEM-WPPANIC
WATERPROOF PANIC



GEM-KEYF
KEYFOB



GEM-TRANSLP LOW PROFILE
WINDOW/DOOR
LESS THAN 1/2" D



GEM-TRANS2
WINDOW/DOOR



**GEM-PIR/
GEM-PIRPET**
PASSIVE



GEM-SMK SMOKE



GEM-DT
DUAL TECHNOLOGY
PIR/MICROWAVE



GEM-RTRANS
RECESSED WINDOW/
DOOR



GEM-GB
ACOUSTIC GLASS
BREAK



GEMC-WL-CO
CARBON MONOXIDE
DETECTOR



GEM-HEAT
DETECTOR