



2111123-1

SL Series RJ45 Coupler, Category 6, unshielded, in-line, black

Body Features

Body Style Inline

Configuration Features

Keyed No
Number of Positions 8
Wiring Pattern One-to-one

Contact Features

Contact Base Material Phosphor bronze
Contact Mating Area Plating Material Gold

Dimensions

PCB Thickness (Recommended) 1.575 mm | 0.062 in

Electrical Characteristics

Contact Resistance 20 m Ohms
Insulation Resistance 500 MOhms
Voltage Rating 150 Vac

Housing Features

Housing Color Black

Industry Standards

Approved Standards ANSI/TIA-568-C.2 | IEC 60603-7
UL Flammability Rating UL 94V-0

Mechanical Attachment

Coupler Style Jack
Mount Cutout Dimensions .582 x .790 in | 14.78 x 20.07 mm

Operation/Application

Plug Insertion Cycles (Min) 750 cycles

2111123-1

Packaging Features

Packaging Method	Bag/Box
Packaging Quantity	25

Product Availability

Region	Asia Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Coupler
Performance Category	Category 6
Shielded	No
Coupler Type	MJ/MJ

Termination Features

Termination Style	SL Termination Tool
-------------------	---------------------

Usage Conditions

Operating Temperature	-10 – 60 °C 14 – 140 °F
Relative Humidity (Operating)	10 – 90 %

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant