



2160046-1

Fiber Optic Patch Cord, OM4, LC duplex to LC duplex, 1.8 mm LSZH, 1 m, aqua

Body Features

| | |
|-------------------------|---------------|
| Cable Color | Aqua |
| Boot Color (End A) | Blue |
| Boot Color (End B) | Blue |
| Boot Type (End A) | Bend limiting |
| Boot Type (End B) | Bend limiting |
| Connector Color (End A) | Beige |
| Connector Color (End B) | Beige |

Configuration Features

| | |
|------------------------------|--------------|
| Number of Fibers | 2 |
| Number of Connectors (End A) | 2 |
| Number of Connectors (End B) | 2 |
| Exit Angle to Exit Angle | 180° to 180° |

Dimensions

| | |
|----------------------|--------------------------------|
| Assembly Length | 1.00 m 3.28 ft |
| Cable Outer Diameter | .071 x .147 in 1.8 x 3.75 mm |

Industry Standards

| | |
|---------------------|------|
| Flammability Rating | LSZH |
|---------------------|------|

Product Availability

| | |
|--------|------|
| Region | EMEA |
|--------|------|

Product Type Features

| | |
|-------------------------|---------------------|
| Product Type | Patch Cord (duplex) |
| System | MPOptimate® |
| Connector Type (End A) | LC/UPC |
| Connector Type (End B) | LC/UPC |
| Fiber Type | OM4 |
| Fiber Diameter | 50/125 µm |
| Connector Style (End A) | Duplex |
| Connector Style (End B) | Duplex |
| Ferrule Material | Zirconia |
| Fiber Cable Buffering | Tight buffer |
| Fiber Cable Type | Duplex, dualzip |

2160046-1

| | |
|--------------|--------------|
| Optical Mode | Multimode |
| Polarity | Pair Flipped |

Signal Characteristics

Insertion Loss, maximum (End A) 0.15 dB
Insertion Loss, maximum (End B) 0.15 dB

Regulatory Compliance/Certifications

| | |
|-----------------|-----------------------|
| Agency | Classification |
| RoHS 2011/65/EU | Compliant |

* Footnotes

| | |
|-----------------|---|
| Assembly Length | Assembly length includes the breakout lengths |
|-----------------|---|