



SPECIFICATION SHEET

09-K1600



G-TEK® KEV™ SEAMLESS KNIT KEVLAR® BLENDED GLOVE WITH NITRILE COATED FOAM GRIP ON PALM & FINGERS – 13 GAUGE, TOUCH SCREEN COMPATIBLE

- Seamless knit construction provides comfort without sacrificing dexterity
- Kevlar® fiber shell provides high tensile strength relative to its weight, is inherently cut resistant and will not melt, ignite or conduct electricity
- Foam nitrile coatings are compatible with light oils and will provide a good grip and excellent abrasion resistance
- Touch screen compatible to allow the user to operate a touch screen phone or device without removing gloves
- Knit wrist helps prevent dirt and debris from entering the glove
- Cotton color binding denotes sizing
- Launderable for extended life and to reduce replacement costs

APPLICATIONS

- Automotive
- Metal stamping
- Material handling
- Glass handling operations
- Fishing industries
- Sanitation
- General maintenance
- Waste handling
- Recycling

CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin extract using high speed. Tumble dry on low to medium heat setting. Can be dry cleaned. Do not bleach.

TECHNICAL DATA

MATERIAL	Kevlar® / Nylon / Steel Fiber / Nitrile Coating				
COLOR	Shell: Yellow/Black / Coating: Black				
CUFF STYLE	Elastic knit				
SIZES	S - XXL				
PACKAGING	1 pair per bag, 12 pairs per dozen, 6 dozen per case				
CASE DIMENSIONS	16.9" x 12.2" x 9.8" / 43cm x 31cm x 25cm				
CASE WEIGHT	S	M	L	XL	XXL
	7.7 lbs	8.2 lbs	9.6 lbs	9.9 lbs	10.4 lbs
	3.5 kg	3.7 kg	4.2 kg	4.5 kg	4.7 kg
COO	China				

PERFORMANCE PROPERTIES

EN388: 4532	ASTM F2992-15 ANSI Cut Level A7 (Adopted by ANSI/ISEA 02/16)					
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-




BARCODES

ITEM	BAG	DOZEN	CASE
09-K1600/S	616314207921	01616314207920	02616314207929
09-K1600/M	616314207914	01616314207913	02616314207912
09-K1600/L	616314207907	01616314207906	02616314207905
09-K1600/XL	616314207938	01616314207937	02616314207936
09-K1600/XXL	616314207945	01616314207944	02616314207943

DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	8.7 / 22.2	9.1 / 23.2	9.9 / 25.2	10.3 / 26.2	10.5 / 26.8
B	3.5 / 9	3.7 / 9.5	4.1 / 10.5	4.3 / 10.8	4.4 / 11.2
H	White	Green	Brown	Yellow	Black



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.