

959385-6

**RJ45 Patch Cord, category 6, shielded, white, 6 m**



## Body Features

|                    |          |
|--------------------|----------|
| Cable Color        | White    |
| Shield Style       | S/FTP    |
| Conductor Material | Copper   |
| Conductor Type     | Stranded |

## Configuration Features

|                           |              |
|---------------------------|--------------|
| Configuration             | Double-ended |
| Keyed                     | No           |
| Number of Positions       | 4-pair       |
| Number of Power Positions | 0            |

## Dimensions

|                                |                               |
|--------------------------------|-------------------------------|
| Length                         | 6.000 m   19.685 ft           |
| Overall Outside Cable Diameter | 5.900 mm   0.232 in           |
| Wire Size (CMA)                | .129 mm <sup>2</sup>   26 AWG |

## Industry Standards

|                     |                               |
|---------------------|-------------------------------|
| Flammability Rating | LSZH (Low Smoke Zero Halogen) |
|---------------------|-------------------------------|

## Operation/Application

|              |    |
|--------------|----|
| Halogen Free | No |
|--------------|----|

## Packaging Features

|                  |     |
|------------------|-----|
| Packaging Method | Bag |
|------------------|-----|

## Product Availability

|        |      |
|--------|------|
| Region | Asia |
|--------|------|

## Product Type Features

|                         |                   |
|-------------------------|-------------------|
| Product Type            | Patch Cord        |
| Assembly Type           | Plug to Plug      |
| Connector Type (End A)  | RJ45 Modular Plug |
| Connector Type (End B)  | RJ45 Modular Plug |
| Performance Category    | Category 6        |
| Cable Assembly Category | Industry Standard |
| Shielded                | Yes               |

959385-6

## Usage Conditions

Operating Temperature Range -20 – 60 °C

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant