



SPECIFICATION SHEET

16-815



3543

G-TEK® POLYKOR SEAMLESS KNIT GLOVE WITH ACRYLIC LINING AND DOUBLE-DIPPED LATEX COATING

- Seamless construction offers increased comfort and breathability
- PolyKor™ shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Double-dipped latex "Micro-Surface" coated palm and knuckles help extend the life of the glove and provide excellent abrasion resistance
- Knit wrist helps prevent dirt and debris from entering the glove
- Washable, resistant to chemicals, water, and ultraviolet light

APPLICATIONS

- Electronics
- Glass cutting
- Sheet metal handling
- Parts assembly
- Sharp small parts handling
- Construction
- General duty applications

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C).

TECHNICAL DATA

MATERIAL	13 gauge PolyKor™ outer shell / acrylic inner shell with latex				
COLOR	Shell: ☐ Salt & Pepper / Coating: ☒ Black				
CUFF STYLE	Continuous knit				
SIZES	S - XXL				
PACKAGING	12 pair per dozen, 6 dozen per case				
CASE SIZE	22.4" x 12.2" x 8.7" / 57cm x 31cm x 22cm				
CASE WEIGHT	S	M	L	XL	XXL
	12.4 lbs 5.7 kg	12.7 lbs 5.8 kg	13 lbs 5.9 kg	14.2 lbs 6.4 kg	15.3 lbs 6.9 kg
COO	China				

PERFORMANCE PROPERTIES

EN388: 3543 ASTM F2992-15 ANSI Cut Level A3 (Adopted by ANSI/ISEA 02/16)
ASTM F1790-05 ANSI Cut Level 3

ABRASION	0	1	2	3	4	—
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	—
PUNCTURE	0	1	2	3	4	—


BARCODES

ITEM	BAG	DOZEN	CASE
☐ 16-815/S	---	01616314131041	02616314131040
☐ 16-815/M	---	01616314131034	02616314131033
☐ 16-815/L	---	01616314131027	02616314131026
☐ 16-815/XL	---	01616314131058	02616314131057
☐ 16-815/XXL	---	01616314131065	02616314131064



DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	9.6 / 24.5	10 / 25.5	10.4 / 26.5	10.8 / 27.5	11.2 / 28.5
B	3.6 / 9.2	3.7 / 9.5	3.9 / 9.8	4.1 / 10.4	4.3 / 10.8
H	☒ Red	☒ Yellow	☒ Brown	☒ Black	☒ Sky Blue



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.