



SPECIFICATION SHEET

16-X320



4543

G-TEK® POLYKOR™ XRYSTAL™ SEAMLESS KNIT GLOVE WITH NITRILE COATED FOAM GRIP – 13 GAUGE

- Seamless construction offers increased comfort and breathability
- PolyKor™ Xrystal™ shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Foam Nitrile coatings are compatible with light oils and will provide a good grip and excellent abrasion resistance
- Cotton color binding denotes sizing
- Washable, resistant to chemicals, water, and ultraviolet light
- Compliant with FDA Part 177 - Indirect food activities: Polymers. Subpart C - Substances for use only as components of articles intended for repeated use. Sec. 177.2600

APPLICATIONS

- Finishing & inspection
- Electronics
- General duty
- Small parts assembly
- Construction
- Maintenance

CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin extract using high speed. Tumble dry on low to medium heat setting. Can be dry cleaned. Do not bleach.

TECHNICAL DATA

MATERIAL	PolyKor™ Xrystal™ Engineered Yarn / Nitrile Foam Coating				
COLOR	Shell: ■ Gray / Coating: ■ Black				
CUFF STYLE	Elastic knit				
SIZES	XS - XXL				
PACKAGING	1 pair per bag, 12 pairs per dozen, 6 dozen per case				
CASE DIMENSIONS	16.9" x 12.2" x 9.8" / 43cm x 31cm x 25cm				
CASE WEIGHT	S	M	L	XL	XXL
	7.7 lbs 3.5 kg	8.2 lbs 3.7 kg	9.6 lbs 4.2 kg	9.9 lbs 4.5 kg	10.4 lbs 4.7 kg
COO	China				

PERFORMANCE PROPERTIES

EN388: 4543	ASTM F2992-15 ANSI Cut Level A4 (Adopted by ANSI/ISEA 02/16)					
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-




BARCODES

ITEM	BAG	DOZEN	CASE
■ 16-X320/XS	616314214370	01616314214379	02616314214378
■ 16-X320/S	616314214356	01616314214355	02616314214354
■ 16-X320/M	616314214349	01616314214348	02616314214347
■ 16-X320/L	616314214332	01616314214331	02616314214330
■ 16-X320/XL	616314214363	01616314214362	02616314214361
■ 16-X320/XXL	616314214387	01616314214386	02616314214385

DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	8.9 / 22.5	9.4 / 24	9.6 / 24.5	10 / 25.5	10.4 / 26.5	10.6 / 26.9
B	3.7 / 9.4	3.9 / 9.8	4 / 10.2	4.2 / 10.6	4.4 / 11.2	4.6 / 11.7
H	■ Purple	■ Red	■ Yellow	■ Brown	■ Black	■ Light Blue



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.