


760077792 | 3061A WH 4/24 R4000  
**PowerSUM 3061A ETL Verified Category 5e U/UTP Cable, low smoke zero halogen, white jacket, 4 pair count, 4000 ft (1,220 m) length, reel**

## Cross Section Drawing



## Construction Materials

Jacket Material	Low Smoke Zero Halogen (LSZH)
Conductor Material	Bare copper
Insulation Material	Polyolefin

## Dimensions

Cable Length	1219 m   4000 ft
Cable Length Tolerance	±5%
Cable Weight	20.00 lb/kft
Diameter Over Jacket	5.207 mm   0.205 in
Jacket Thickness	0.533 mm   0.021 in

## Electrical Specifications

ANSI/TIA Category	5e
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	9.38 ohms/100 m
Mutual Capacitance	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	69 %
Operating Frequency, maximum	200 MHz
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2   CENELEC EN 50288-3-1   ISO/IEC 11801 Class D

760077792 | 3061A WH 4/24 R4000

## Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Acid Gas Test Method	IEC 60754-2
Flame Test Method	IEC 60332-3-22
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Smoke Test Method	IEC 61034-2

## General Specifications

Cable Type	U/UTP (unshielded)
Pairs, quantity	4
Cable Component Type	Horizontal
Packaging Type	Reel
Brand	PowerSUM   SYSTIMAX®
Jacket Color	White
Product Number	3061A
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

## Mechanical Specifications

Pulling Tension, maximum	11 kg   25 lb
--------------------------	---------------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

