



SPECIFICATION SHEET

19-D334



G-TEK® 3GX 13 GAUGE DYNEEMA® DIAMOND BLENDED SHELL WITH FOAM NITRILE COATED PALM

- Seamless construction offers increased comfort and breathability
- Dyneema® Diamond blended shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Foam nitrile coated palm is compatible with light oils and will provide a good grip and excellent abrasion resistance
- Washable, resistant to chemicals, water, and ultraviolet light
- Made from component materials which comply with Federal regulations for food contact. 21 CFR, 170-199
- Color coded hems for easy size identification
- Knit Wrist helps prevent dirt and debris from entering the glove

APPLICATIONS

- Electronics
- Glass cutting
- Sheet metal handling
- Parts assembly
- Sharp small parts handling
- Construction and general duty

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C)

TECHNICAL DATA

MATERIAL	Shell: Dyneema® Diamond / Coating: Foam nitrile			
COLOR	Shell: ■ Salt & Pepper / Coating: ■ Black			
CUFF STYLE	Continuous knit			
SIZES	S - XL			
PACKAGING	12 pairs per dozen, 6 dozen per case			
CASE	11.8" x 12.6" x 14.2" / 30cm x 32cm x 36cm			
CASE WEIGHT	S	M	L	XL
	12.1 lbs 5.5 kg	13.2 lbs 6.0 kg	14.1 lbs 6.4 kg	15.0 lbs 6.8 kg
COO	China			

PERFORMANCE PROPERTIES

EN388: 4443 ASTM F2992-15 ANSI Cut Level A3 (Adopted by ANSI/ISEA 02/16)
ASTM F1790-05 ANSI Cut Level 3

ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5


BARCODES

ITEM	BAG	DOZEN	CASE
■ 19-D334/S	616314167799	01616314167798	02616314167797
■ 19-D334/M	616314167782	01616314167782	02616314167780
■ 19-D334/L	616314167775	01616314167774	02616314167773
■ 19-D334/XL	616314167805	01616314167804	02616314167803



DIMENSIONS (in/cm)

	S	M	L	XL
A	9.1 / 23.0	9.4 / 24.0	9.8 / 25.0	10.2 / 26.0
B	3.9 / 10.0	4.1 / 10.5	4.3 / 11.0	4.5 / 11.5
H	Red	Yellow	Brown	Black



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.