



# SPECIFICATION SHEET

## 19-D475



### MAXICUT® DRY KNIT DYNEEMA® / ENGINEERED YARNS GLOVE WITH NITRILE COATED FOAM GRIP

- Micro-Foam Nitrile coatings are compatible with light oils and will provide a good grip and excellent abrasion resistance
- Knit Wrist helps prevent dirt and debris from entering the glove
- Unique high performance yarns and fibers that offer cut protection while maintaining high levels of comfort
- Reinforcement between the thumb and forefinger, improves cut resistance and extends glove life in an inherently weak area
- Patented micro-foam nitrile coating offers 360° breathability
- Latest knitting technology utilized to produce smooth and rounded fingertips, improving fingertip sensitivity
- Optimized grip delivered through our micro-cup finish
- Dyneema® is a brand of polyethylene fibers that are 10 to 15 times stronger than steel, more durable than polyester and a strength that is 40% greater than aramid fiber

### APPLICATIONS

- Electronics
- Glass cutting
- Metal handling and fabrication
- Food and meat processing

### CARE INSTRUCTIONS

Use commercial laundry soap or detergent (do NOT use dry cleaning solutions). Wash in warm to medium hot water, do not exceed 104°F (40°C). Wash for 10 minutes and rinse in cold water. Repeat wash and rinse if soiling is especially heavy. Tumble dry - maximum temperature 140°F (60°C).

### TECHNICAL DATA

MATERIAL	Shell: Seamless Nylon with Glass/Dyneema®/Lycra® Coating: MicroFoam nitrile palm and knuckle					
COLOR	■ Grey					
CUFF STYLE	Continuous knit					
SIZES	XS - XXL					
PACKAGING	12 pairs per dozen, 12 dozen per case					
CASE	18.5" x 10.5" x 14.0" / 47.0cm x 26.7cm x 35.6cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	10.8 lbs 4.9 kg	11.7 lbs 5.3 kg	12.8 lbs 5.8 kg	13.9 lbs 6.3 kg	15.2 lbs 6.9 kg	16.0 lbs 7.3 kg
COO	Sri Lanka					

### PERFORMANCE PROPERTIES

EN388: 4543	ASTM F2992-15 ANSI Cut Level A4 (Adopted by ANSI/ISEA 02/16) ASTM F1790-05 ANSI Cut Level 4					
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

### BARCODES

ITEM	BAG	DOZEN	CASE
■ 19-D475/XXL	---	01616314053664	02616314053663
■ 19-D475/XL	---	01616314053657	02616314053656
■ 19-D475/L	---	01616314053640	02616314053649




### BARCODES CONT.

■ 19-D475/M	---	01616314053633	02616314053632
■ 19-D475/S	---	01616314053626	02616314053625
■ 19-D475/XS	---	01616314053619	02616314053618

### DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
<b>A</b>	7.7 / 19.5	8.1 / 20.5	8.7 / 22.0	9.1 / 23.0	9.4 / 24.0	9.6 / 24.5
<b>B</b>	3.3 / 8.3	3.4 / 8.7	3.7 / 9.4	3.9 / 10.0	4.1 / 10.3	4.2 / 10.7
<b>H</b>	■ Blue	■ Red	■ Orange	□ White	■ Yellow	■ Grey



**PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®**

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobal.com](http://www.pipglobal.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.