



SPECIFICATION SHEET

20-D SERIES



KUT-GARD® SINGLE-PLY FILAMENT DYNEEMA® SLEEVE

- Provides cut and abrasion resistance for light duty applications
- Seamless construction offers increased comfort and breathability
- Elastic ends for a snug fit and to eliminate debris from entering
- Color coded hems for easy size identification
- Launderable for extended life and to reduce replacement costs
- Made from component materials which comply with Federal regulations for food contact 21CFR 170-199

APPLICATIONS

- Food Processing
- Electronics Manufacturing
- Glass Cutting
- Paper Processing

CARE INSTRUCTIONS

Recommend washing sleeves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Hang dry; tumble dry is not recommended.

TECHNICAL DATA

MATERIAL	100% Dyneema®				
COLOR	□ White				
CUFF STYLE	Knit elasticized ends				
SIZES	10", 12", 16", 18", 20"				
PACKAGING	1 each per bag, 144 each per case				
CASE SIZE	51.3cm x 35cm x 41.5cm / 20" x 13" x 16"				
CASE WEIGHT	10"	12"	16"	18"	20"
	10.1 lbs 4.6 kg	12.6 lbs 5.7 kg	12.6 lbs 5.7 kg	12.6 lbs 5.7 kg	12.6 lbs 5.7 kg
COO	USA				

CUT RESISTANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 2

BARCODES

ITEM	EACH	DOZEN	CASE
□ 20-D10	----	01616314037184	02616314037184
□ 20-D12	----	01616314037191	02616314037191
□ 20-D16	----	01616314037207	02616314037207
□ 20-D18	----	01616314037214	02616314037214
□ 20-D20	----	01616314037221	02616314037221



DIMENSIONS (in/cm)

	10"	12"	16"	18"	20"
A	10 / 25.4	12 / 30.5	16 / 40.6	18 / 45.7	20 / 50.8
B	4.2 / 10.7	4.5 / 11.5	4.7 / 11.9	4.9 / 12.5	4.9 / 12.5

