



# SPECIFICATION SHEET

## 20-SD SERIES



### KUT-GARD® 2-PLY SPUN DYNEEMA® / NYLON BLEND SLEEVE

- Spun Dyneema® and nylon blend
- Offers unparalleled comfort and coolness while providing cut and abrasion resistance
- Seamless construction for comfort, fit and dexterity
- Elastic ends for a snug fit and to eliminate debris from entering
- Special non-latex cuff made of lycra, dramatically reduces cuff blow-out, even after multiple launderings in bleach
- Color coded hems for easy size identification
- Launderable for extended life and to reduce replacement costs

### APPLICATIONS

- Food Processing
- Electronics Manufacturing
- Glass Cutting
- Paper Processing

### CARE INSTRUCTIONS

Recommend washing sleeves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Hang dry; tumble dry is not recommended.

### TECHNICAL DATA

|             |                                      |
|-------------|--------------------------------------|
| MATERIAL    | 50% Dyneema® / 50% Nylon blend       |
| COLOR       | <input type="checkbox"/> White       |
| CUFF STYLE  | Knit elasticized ends                |
| SIZES       | 14", 16", 18"                        |
| PACKAGING   | 1 each per bag, 144 each per case    |
| CASE SIZE   | 30.5cm x 15cm x 15cm / 12" x 6" x 6" |
| CASE WEIGHT | 3.6 lbs / 1.6 kg                     |
| COO         | USA                                  |

### CUT RESISTANCE PROPERTIES

- Method ASTM F1790-04
- 600 grams
- EN388 Level 3 Cut Score

### BARCODES

| ITEM                             | EACH | DOZEN          | CASE           |
|----------------------------------|------|----------------|----------------|
| <input type="checkbox"/> 20-SD14 | ---  | 01616314051684 | 02616314051683 |
| <input type="checkbox"/> 20-SD16 | ---  | 01616314055415 | 02616314055414 |
| <input type="checkbox"/> 20-SD18 | ---  | 01616314055422 | 02616314055421 |



### DIMENSIONS (in/cm)

|   | 14"        | 16"        | 18"        | --- | --- |
|---|------------|------------|------------|-----|-----|
| A | 14 / 35.6  | 16 / 40.6  | 18 / 45.7  | --- | --- |
| B | 4.5 / 11.5 | 4.7 / 11.9 | 4.9 / 12.5 | --- | --- |

